



EX-Z4V10H 335-11Z-1348/1583-1-3G/D

- Belt speed of up to 1 m/s
- Nylon roller, Ø 22 mm, running surface 95 mm
- 1 NO contact / 1 NC contact at 24° deflection
- Positive-break NC contact for fail-safe switching
- Explosion protection for ATEX Zones 2 and 22
- Metal enclosure
- Good resistance to oil and petroleum spirit
- 40,5 mm x 76 mm x 38 mm
- Actuator heads can be repositioned by 4 x 90°
- Mounting details to EN 50041
- 1 Cable entry M 20 x 1.5
- **only for positioning tasks**

Schmersal Canada Ltd., 29 Centennial Road, Unit 1, Orangeville, Ontario L9W 1R1 Canada

Les données et les valeurs ont été soigneusement vérifiées. Les illustrations peuvent être différentes de l'original. Vous trouverez d'avantage de caractéristiques techniques dans les manuels d'instructions. Sous réserve de modifications techniques et errata.

Généré le: 2025-02-14 09 h 43