

Auswahltafel: Magnetschalter

Schaltabstände																
Betätigungs-magnet	BN 80-10Z	BN 80-01Z	BN 80-rz	BN 85-R	BN 310-10Z BN 310-01Z	BN 310-RZ	BN 32-10 BN 32-01 BN 32-11	BN 32-R BN 32-11R	BN 325-R	BN 65-10Z BN 65-10Z/1 BN 65-01Z	BN 65-RZ	BN 65-10Z/V BN 65-01Z/V	BN 65-RZ/V	BN 20-10Z BN 20-20Z BN 20-01Z BN 20-02Z BN 20-11Z	BN 20-RZ BN 20-2RZ BN 20-11RZ	
BP 6 S				4-18	2-12											
BP 7 S				6-22												
BP 8	3-8	0-5			2-10											
BP 8 S																
BP 10	6-12	2-9	2-9		5		5			5						
BP 10 N						15		10	10		15					5
BP 10 S				10-30	5-20	15		10	10		15	5				5
2 x BP 10	12-20	2-13	2-13		17	20	12	15	15		20			3	12	
2 x BP 10 N						20		15	15		20					10
2 x BP 10 S				12-36	6-27	20		15	15		20	10				10
BP 15	8-14	2-10			6	6				6						
BP 15 N						17		12	12		17					7
BP 15 S				12-30	5-22	17	12	12	12		17	6				7
2 x BP 15	12-22	2-15			17	12				17						
2 x BP 15S				13-38	7-28	17	12			17						12
2 x BP 15/2						22		17	17		22					15
2 x BP 15/2 N						22		17	17		22					15
2 x BP 15/2 S						15-30		10-25	10-25		15-30					15
BP 34					5-20	15				15-20				15		
BP 34 N						15-30		10-25	10-25		15-30					10-25
BP 34 S			20-50	10-40		15-30		10-25	10-25		15-30	20				10-25
2 x BP 34	12-26	5-18			22-60											
BP 20	12-24	0-14			20	15				20				10	15	
BP 20 N						3-25		5-20	5-20		25					15
BP 20 S			10-38	3-28		3-25		5-20	5-20		25	15				15
BP 31	12-24	0-14			20	15				20				10	15	
BP 31 N						3-25		5-20	5-20		25					15
BP 31 S			12-40	4-30		3-25		5-20	5-20		25	15				15
BP 11	22-28	2-16			8-20	5-15				20				15	15	
BP 11 N						15		10	10		15					5
BP 11 S			10-30	4-23		15		10	10		15	5				5
2 x BP 11 N						3-25		20	20		25					15
2 x BP 11 S						3-25		20	20		25	15				15
BP 12	24-32	4-20			10-30	10-25				10-30				20	25	
BP 12 N						20		15	15		20					10
2 x BP 12 N						10-30		10-25	10-25		10-30					5-20
2 x BP 12 S						10-30		10-25	10-25		10-30	25				5-20
BP 21					25-50	20-40				25-50				45	20-45	
BP 21 N						15-45		15-40	15-40		15-45					10-35
BP 21 S						15-45		15-40	15-40		15-45	30				10-35
2 x BP 21 N						20-60		20-55	20-55		20-60					15-50
2 x BP 21 S						20-60		20-55	20-55		20-60	20-55				15-50
BP 22 S												25				
BP 22 N+BP 22 S												35				
2 x BP 22 S												15-55				
BE 20					20	15							10	15		
BE 20 N						20		15	15		20					10
BE 20 S						20		15	15		20	6				10