



CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

本翻译文件不具有法律效力，
不得单独使用
This translated document
does not have legal validity and
cannot be used in isolation

CERTIFICATE NO.: 2024010305668990

NAME AND ADDRESS OF THE APPLICANT

K.A. Schmersal GmbH & Co. KG
Moeddinghofe 30, D-42279 Wuppertal, Germany

NAME AND ADDRESS OF THE MANUFACTURER

K.A. Schmersal GmbH & Co. KG
Moeddinghofe 30, D-42279 Wuppertal, Germany

NAME AND LOCATION OF THE FACTORY

K.A. Schmersal GmbH & Co. KG
Moeddinghofe 30, D-42279 Wuppertal, Germany

PRODUCT NAME,MODEL AND SPECIFICATION

Limit switch

Z/T.335/336/355 : Ui: 500V,250V For three contacts , 50V For Connector Version; Uimp:6kV,4kV For three contacts , 0.8kV For Connector Version; Ith:10A; AC-15:Ue/Ie:230V/4A; DC-13:Ue/Ie:24V/1A; Connector Version:AC-15:Ue/Ie:50VAC/4A; IP67,IP65,IP54

STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB/T 14048.5-2017

This is to certify that the above mentioned product(s) complies with the requirements of implementation rules for compulsory certification(REFNO. CNCA-C03-02:2024).

Valid from: Aug.01,2024

Valid until: Jul.31,2029

The certificate information and validity could be checked by scanning the QR code below or logging in to the website of the issuing authority, or on the website of the CNCA (www.cnca.gov.cn).



SIGNATURE:

谢肇煦



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.





CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

本翻译文件不具有法律效力，
不得单独使用
This translated document
does not have legal validity and
cannot be used in isolation

CERTIFICATE NO. : 2024010305668990

Appendix : Page 1 of 3

Type description :

Annex 1: Ordering Code =
(1)(2)-(3)-(4)(5)(6)-(7)-(8)-(9)-(10)-(11)

Nr.	Option	Description		
(1)	Z	Snap action, direct opening	速动, 具有直接断开功能	
	T	slow action, direct opening	缓动, 具有直接断开功能	
	M	Snap action, no NC contact, no direct opening	速动, 无常闭触头, 不具有直接断开功能	
(2)	S	Plunger S	直杆 S	
	R	Roller Plunger R	滚轮直杆 R	
	K or 1K	Offset Roller Lever K	滚轮偏移 K	
	3K	Angle Roller Lever 3K	滚轮摇臂 3K	
	3V4D	Fork Roller Lever	叉形滚轮摇臂 4D	
	3VS	Actuator for Hinge mounting	用于铰链安装的操作头	
	VH or 4VH	Roller Lever H (*)	滚轮摇臂 H (*)	
	4V1H	Roller Lever H with 4 positions (Diameter 25mm) (*)	滚轮摇臂 H (*)	
	V3H or 4V3H	Roller Lever 3H (*)	滚轮摇臂 3H (*)	
	4V4H	Antenna Lever 4H (*)	滚轮摇臂 4H (*)	
	V7H or 4V7H	Roller Lever 7H (*)	滚轮摇臂 7H (*)	
	4V8H	Swivel Lever 8H (*)	滚轮摇臂 8H (*)	
	V9H or 4V9H	Rod Lever 9H (*)	滚轮摇臂 9H (*)	
	V10H or 4V10H	Rod Lever 10H (*)	滚轮摇臂 10H (*)	
			(*) Prefix "4": Actuator head can be rotated by 4x90°	前缀“4”, 操作头可以旋转 4x90°
		V8S or V10S	Shaft Actuator for hinges (Diameters 8mm or 10mm)	用于铰链的轴操动 (直径 8mm 或 10mm)
		. or V. (= "dot")	Switch without actuator; to be completed with one of the actuators mentioned above	开关无操动头, 可配合以上提到的操动头
	(3)	335	Metal enclosure; dimensions according DIN EN 50041; 40,5 mm x 76 mm x 38 mm	金属外壳; 尺寸根据 DIN EN 50041; 40,5 mm x 76 mm x 38 mm
		336	Thermoplastic enclosure; dimensions according DIN EN 50041; 40,5 mm x 76 mm x 38 mm	热塑外壳; 尺寸根据 DIN EN 50041; 40,5 mm x 76 mm x 38 mm
		355	Metal enclosure; dimensions according DIN EN 50041; 66,7 mm x 76 mm x 38 mm	金属外壳; 尺寸根据 DIN EN 50041; 66,7 mm x 76 mm x 38 mm

This page is attached to the certificate and should be used at the same time as the certificate page.



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.



CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

本翻译文件不具有法律效力，
不得单独使用
This translated document
does not have legal validity and
cannot be used in isolation

CERTIFICATE NO. : 2024010305668990

Appendix : Page 2 of 3

(4)	01	1x NC contact	1 常闭触点	
	02	2x NC contacts	2 常闭触点	
	11	1x NO contact, 1x NC contact	1 常开, 1 常闭触点	
	20	2x NO contacts	2 常开触点	
	01/01	1x NC contact left, 1x NC contact right	1 常闭触点(左侧), 1 常闭触点(右侧)	
	12	1x NO contact, 2x NC contacts (only with 335, 355)	1 常开, 2 常闭触点(仅针对 335, 355 系列)	
	03	3x NC contacts (only with 335, 355)	3 常闭触点(仅针对 335, 355 系列)	
	(5)	X	IP 54 Protection	IP 54
		Y	IP 65 Protection	IP 65
Z		IP 67 Protection	IP 67	
Blank		IP 00 Protection	IP 00	

Ordering Code continued

(6)	Blank	Standard	标准类型
	H	Staggered contacts (slow action only)	非同步触头(仅针对缓动)
	UE	Overlapping contacts (slow action only)	交错触头(仅针对缓动)
	R	Latching of Actuator (will cause IP65 protection)	手动复位
	Z	Additional sealing of actuator (only V*H actuators)	操动件密封
(7)	Blank	Standard	标准类型
	G24	With LED	带 LED
(8)	Blank or M20	Cable entry M20	M20 接线孔
	NPT	Cable entry NPT 1/2"	NPT 接线孔
	ST	M12 connector with A-coding	连接器 M12(A 编码)
	ST-2310	M12 connector with B-coding	连接器 M12(B 编码)
(9)	Blank	Actuator without roll or actuator with plastic roll	不带滚轮或带塑料轮
	RMS	Actuator with brass roll	黄铜轮
	RVA	Actuator with stainless steel roll	不锈钢轮

This page is attached to the certificate and should be used at the same time as the certificate page.



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.



CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

本翻译文件不具有法律效力，
不得单独使用
This translated document
does not have legal validity and
cannot be used in isolation

CERTIFICATE NO. : 2024010305668990

Appendix : Page 3 of 3

(10)	Blank	Angle of actuator = 0°	附件壳不转动
	U90	Angle of actuator = 90° (clockwise)	附件壳顺时针转 90°
	U180	Angle of actuator = 180° (clockwise)	附件壳顺时针转 180°
	U270	Angle of actuator = 270° (clockwise)	附件壳顺时针转 270°
(11)	Blank	Standard type	标准类型
	xxxx-xx	Indicator for minor customer-specific design change, without change for function or structure;	针对客户特殊需求，不改变产品结构和功能

This page is attached to the certificate and should be used at the same time as the certificate page.



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.