



CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

本翻译文件不具有法律效力，
不得单独使用
This translated document
does not have legal validity and
cannot be used in isolation

CERTIFICATE NO.: 2024010305669636

NAME AND ADDRESS OF THE APPLICANT

K.A. Schmersal GmbH & Co. KG
Moeddinghofe 30, D-42279 Wuppertal, Germany

NAME AND ADDRESS OF THE MANUFACTURER

K.A. Schmersal GmbH & Co. KG
Moeddinghofe 30, D-42279 Wuppertal, Germany

NAME AND LOCATION OF THE FACTORY

K.A. Schmersal GmbH & Co. KG
Im Ostpark 2, D-35435 Wettenberg, Germany

PRODUCT NAME,MODEL AND SPECIFICATION

Hinge Safety Switch
TESK...;Ui:300V;Uimp:2.5kV;AC-15:230VAC/2A ; Ith: 2.5A ; IP65;See the appendix

STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB/T 14048.5-2017

This is to certify that the above mentioned product(s) complies with the requirements of implementation rules for compulsory certification(REFNO. CNCA-C03-02:2024).

Valid from: Aug.02,2024

Valid until: Aug.01,2029

The certificate information and validity could be checked by scanning the QR code below or logging in to the website of the issuing authority, or on the website of the CNCA (www.cnca.gov.cn).



SIGNATURE:

谢肇煦



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.





CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

本翻译文件不具有法律效力，
不得单独使用
This translated document
does not have legal validity and
cannot be used in isolation

CERTIFICATE NO. : 2024010305669636

Appendix : Page 1 of 1

Type description :

Ordering Code =		TESK-(1)(2)-(3)(4)-(5)	
Nr.	Option	Description	描述
(1)	S	Standard Hinge	标准铰链
	L	Long Hinge	长铰链
(2)	A	Preset for Outdoor Mounting	预置室外安装
	I	Preset for Indoor Mounting	预置室内安装
	U	Switching Angle to be set on site	现场设置切换角度
(3)	22	2 NO contacts / 2 NC contacts	2 常开, 2 常闭触点
	12	1 NO contact / 2 NC contacts	1 常开, 2 常闭触点
	13	1 NO contact / 3 NC contacts	1 常开, 3 常闭触点
	02	2 NC contacts	2 常闭触点
	11	1 NO contact / 1 NC contact	1 常开, 1 常闭触点
(4)	L1	Cable outlet at bottom	底部的电缆出口
	L2	Cable outlet at top	顶部的电缆出口
	ST1	Connector at bottom	底部的连接器
	ST2	Connector at top	顶部的连接器
(5)	3m	Cable length 3 m (only for L1 / L2)	电缆长度 3 米 (仅适用于 L1 / L2)
	5m	Cable length 5 m (only for L1 / L2)	电缆长度 5 米 (仅适用于 L1 / L2)
	10m	Cable length 10 m (only for L1 / L2)	电缆长度 10 米 (仅适用于 L1 / L2)
	20m	Cable length 20 m (only for L1 / L2)	电缆长度 20 米 (仅适用于 L1 / L2)
	30m	Cable length 30 m (only for L1 / L2)	电缆长度 30 米 (仅适用于 L1 / L2)

This page is attached to the certificate and should be used at the same time as the certificate page.



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.