



CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

本翻译文件不具有法律效力，
不得单独使用
This translated document
does not have legal validity and
cannot be used in isolation

CERTIFICATE NO.: 2024010305669667

NAME AND ADDRESS OF THE APPLICANT

K.A. Schmersal GmbH & Co. KG
Moeddinghofe 30, D-42279 Wuppertal, Germany

NAME AND ADDRESS OF THE MANUFACTURER

K.A. Schmersal GmbH & Co. KG
Moeddinghofe 30, D-42279 Wuppertal, Germany

NAME AND LOCATION OF THE FACTORY

K.A. Schmersal GmbH & Co. KG
Moeddinghofe 30, D-42279 Wuppertal, Germany

PRODUCT NAME,MODEL AND SPECIFICATION

Limit switch

T/M 035 : Ui: 500V(type “11” contact); 400V(type “02” or “20” contacts) ; Ith:10A ;
AC-15:Ue/Ie:400V/4A (type T switches); 400V/2.5A(type M switches) ; IP67 ; See the appendix

STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB/T 14048.5-2017

This is to certify that the above mentioned product(s) complies with the requirements of
implementation rules for compulsory certification(REFNO. CNCA-C03-02:2024).

Valid from: Aug.02,2024

Valid until: Aug.01,2029

The certificate information and validity could be checked by scanning the QR code below or logging in to
the website of the issuing authority, or on the website of the CNCA (www.cnca.gov.cn).



SIGNATURE:

谢肇煦



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.





CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

本翻译文件不具有法律效力，
不得单独使用
This translated document
does not have legal validity and
cannot be used in isolation

CERTIFICATE NO. : 2024010305669667

Appendix : Page 1 of 2

Type description :

Ordering Code		= (1)2L 035-(2)Z-(3)	
Nr.	Option	Description	描述
(1)	T	Slow action, direct opening	缓动, 具有直接断开功能
	M	snap action, no direct opening	速动, 不具有直接断开功能
(2)	02	2x NC contacts	2 常闭触点
	11	1x NC contact, 1x NO contact	1 常开, 1 常闭触点
	20	2x NO contact	2 常开触点
(3)	Blank	Standard	标准类型
	UE	Overlapping Contacts	交错触头
	M20	Cable Gland M20 (M25 is standard)	电缆接头 M20 (M25 是标准配置)
	RVA	Actuator with stainless steel roll	不锈钢滚轮
	C	Magnetic blow-out	磁灭弧
	1732	Switch with higher actuation forces	开关具有更高的操动力

This page is attached to the certificate and should be used at the same time as the certificate page.



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.



CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

本翻译文件不具有法律效力，
不得单独使用
This translated document
does not have legal validity and
cannot be used in isolation

CERTIFICATE NO. : 2024010305669667

Appendix : Page 2 of 2

Ordering Code		=	(1)2L 035-(2)Z-(3)
Nr.	Option	Description	描述
(1)	T	Slow action, direct opening	缓动, 具有直接断开功能
	M	snap action, no direct opening	速动, 不具有直接断开功能
(2)	02	2x NC contacts	2 常闭触点
	11	1x NC contact, 1x NO contact	1 常开, 1 常闭触点
	20	2x NO contact	2 常开触点
(3)	Blank	Standard	标准类型
	UE	Overlapping Contacts	交错触头
	M20	Cable Gland M20 (M25 is standard)	电缆接头 M20 (M25 是标准配置)
	RVA	Actuator with stainless steel roll	不锈钢滚轮
	C	Magnetic blow-out	磁灭弧
	1732	Switch with higher actuation forces	开关具有更高的操动力

This page is attached to the certificate and should be used at the same time as the certificate page.



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.