



CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

本翻译文件不具有法律效力，
不得单独使用
This translated document
does not have legal validity and
cannot be used in isolation

CERTIFICATE NO.: 2024010305669668

NAME AND ADDRESS OF THE APPLICANT

K.A. Schmersal GmbH & Co. KG
Moeddinghofe 30, D-42279 Wuppertal, Germany

NAME AND ADDRESS OF THE MANUFACTURER

K.A. Schmersal GmbH & Co. KG
Moeddinghofe 30, D-42279 Wuppertal, Germany

NAME AND LOCATION OF THE FACTORY

K.A. Schmersal GmbH & Co. KG
Moeddinghofe 30, D-42279 Wuppertal, Germany

PRODUCT NAME,MODEL AND SPECIFICATION

Limit Switch

T/M 015,T/M 016,T/M 017 : Ui:400V(Switches with NO or NC contacts only),500V(All other);Uimp:6kV;Ith:10A;AC-15:Ue/Ie:400VAC/2.5A(Snap action),400VAC/4A(Slow action);IP65

STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB/T 14048.5-2017

This is to certify that the above mentioned product(s) complies with the requirements of implementation rules for compulsory certification(REFNO. CNCA-C03-02:2024).

Valid from: Aug.02,2024

Valid until: Aug.01,2029

The certificate information and validity could be checked by scanning the QR code below or logging in to the website of the issuing authority, or on the website of the CNCA (www.cnca.gov.cn).



SIGNATURE:

谢肇煦



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.





CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

本翻译文件不具有法律效力，
不得单独使用
This translated document
does not have legal validity and
cannot be used in isolation

CERTIFICATE NO. : 2024010305669668

Appendix : Page 1 of 2

Type description :

Type Designation: (1)(2) (3) -(4) Y-(5)-(6)

Remark: In some cases "M20" is added to the description for the cable gland

Nr.	Option	Description	描述	Remark 备注
(1)	T	Slow action	缓动	
	M	Snap action	速动	
(2)	S	Plunger S	直杆 S	
	2S	Telescopic plunger 2S	加长直杆 2S	
	K	Offset roller lever K	滚轮偏移 K	
	2K	Rocking offset roller lever 2K	滚轮摇臂 2K	
	3K	Angle roller lever 3K	滚轮摇臂 3K	
	VH	Roller lever H	滚轮摇臂 H	
	V2H	Leaf-spring lever 2H	弹簧杆 2H	
	V3H	Roller lever 3H	滚轮摇臂 3H	
	V4H	Spring rod lever on shaft 4H	弹簧杆 4H	
	V6H	Leaf-spring lever 6H	弹簧杆 6H	
	V7H	Roller lever 7H	滚轮摇臂 7H	
	V8H	Roller lever 8H	滚轮摇臂 8H	
	V9H	Rod lever 9H	长杆摇臂 9H	
	V10H	Rod lever 10H	长杆摇臂 10H	
	V. (="V dot")	Switch without actuator; to be completed with one of the actuators H/2H/3H...10H	开关无操动机构,带以上提到的任一操动件将是完整的	

This page is attached to the certificate and should be used at the same time as the certificate page.



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.



CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

本翻译文件不具有法律效力，
不得单独使用
This translated document
does not have legal validity and
cannot be used in isolation

CERTIFICATE NO. : 2024010305669668

Appendix : Page 2 of 2

(3)	015	2 contacts, basic switch size 67x75x43	2个触点,基本开关尺寸67x75x43	
	016	3 contacts, basic switch size 67x152x43	3个触点,基本开关尺寸67x152x43	
	017	4 contacts, basic switch size 67x130x43	4个触点,基本开关尺寸67x130x43	
(4)	11	1 NO contact / 1 NC contact	1常开,1常闭触点	
	02	2 NC contacts	2常闭触点	U _i = 400V
	20	2 Normally open contacts	2常开触点	U _i = 400V
	12	1 NO contact / 2 NC contacts	1常开,2常闭触点	
	21	2 Normally open contacts, 1 Normally closed contact	2常开,1常闭触点	
	03	3 NC contacts	3常闭触点	U _i = 400V
	30	3 Normally open contacts	3常开触点	U _i = 400V
	22	2 NO contacts / 2 NC contacts	2常开,2常闭触点	
	13	1 NO contact / 3 NC contacts	1常开,3常闭触点	
	31	3 NO contacts / 1 NC contact	3常开,1常闭触点	
(5)	UE	Slow action with overlapping contacts	交错触头	
	H	Slow action with staggered contacts	非同步触头	
	C	Magnetic blow-out	磁力爆裂	
(6)	xxxx-xx	Indicator for minor customer -specific design change, without change for function or structure	针对客户特殊需求,不改变产品结构和功能	

This page is attached to the certificate and should be used at the same time as the certificate page.



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.