



CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

本翻译文件不具有法律效力，
不得单独使用
This translated document
does not have legal validity and
cannot be used in isolation

CERTIFICATE NO.: 2024010303668554

NAME AND ADDRESS OF THE APPLICANT

K.A. Schmersal GmbH & Co. KG
Moedinghofe 30, D-42279 Wuppertal, Germany

NAME AND ADDRESS OF THE MANUFACTURER

K.A. Schmersal GmbH & Co. KG
Moedinghofe 30, D-42279 Wuppertal, Germany

NAME AND LOCATION OF THE FACTORY

K.A. Schmersal GmbH & Co. KG
Im Ostpark 2, D-35435 Wettenberg, Germany

PRODUCT NAME,MODEL AND SPECIFICATION

Relay

SRB301HC/T-24V,SRB301HC/T-24V-(V.2),SRB301HC/R-24V,SRB301ST-24V,SRB301ST-24V-(V.2),SRB301MC-24V,SRB301MC-ST-24V,SRB200X2-24V,SRB301HC/T-230V,SRB301HC/R-230V,SRB324ST-24V :
Ui:250V;Uimp:4kV;AC-15:Ue/Ie:230V/6A ; DC-13:Ue/Ie:24V/6A ; Ith:8A ; shell IP40,terminal IP20

STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB/T 14048.5-2017

This is to certify that the above mentioned product(s) complies with the requirements of implementation rules for compulsory certification(REFNO. CNCA-C03-02:2024).

Valid from: Jul.31,2024

Valid until: Jul.30,2029

The certificate information and validity could be checked by scanning the QR code below or logging in to the website of the issuing authority, or on the website of the CNCA (www.cnca.gov.cn).



SIGNATURE:

谢肇煦



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.





CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

本翻译文件不具有法律效力，
不得单独使用
This translated document
does not have legal validity and
cannot be used in isolation

CERTIFICATE NO. : 2024010303668554

Appendix: Page 1 of 1

Type description :

SRB	a	b	c	dd	eee
1	2	3	4	5	6
1.	SRB- basic type	基本类型			
2.	2 - 2 Stop 0 Contacts	2 安全触点 停止类别 0			
	3 - 3 Stop 0 Contacts	3 安全触点 停止类别 0			
3.	0 - 0 Stop 1 Contacts	0 停止 1 个联系人			
	2 - 2 Stop 1 Contacts	2 停止 1 个联系人			
4.	0 - 0 Auxiliary Contact	0 辅助触点			
	1 - 1 Auxiliary Contact	1 辅助触点			
	4 - 4 Auxiliary Contacts	4 辅助触点			
5.	ST - Standard	标准			
	MC - Medium Comfort	中度舒适			
	MC-ST - Medium Comfort with Screw connection, plug-in	中等舒适, 带螺钉连接, 插入式			
	HC/T - High Comfort / Test	高舒适度/测试			
	HC/R - High Comfort / Reset	高舒适度/重置			
	X2 Alternative circuit layout	可替换的电路布局			
6.	Supply-voltage	电源电压			
	24V: SRB301HC/T-24V, SRB301HC/R-24V, SRB301MC-24V, SRB301MC-ST-24V, SRB200X2, SRB301ST, SRB324ST-24V				
	48V...240V: SRB301HC/T-230V, SRB301HC/R-230V				
	Additional "(V.2)" means updated internal circuit without change of major properties 附加 "- (V.2)" 表示更新软件的版本, 和结构无关				

This page is attached to the certificate and should be used at the same time as the certificate page.



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.