



CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

本翻译文件不具有法律效力，
不得单独使用
This translated document
does not have legal validity and
cannot be used in isolation

CERTIFICATE NO.: 2024010305649334

NAME AND ADDRESS OF THE APPLICANT

Schmersal Industrial Switchgear (Shanghai) Co.,Ltd.
No.3336 Caoying Road, Qingpu, Shanghai, P.R.China

NAME AND ADDRESS OF THE MANUFACTURER

K.A. Schmersal GmbH & Co. KG
Moeddinghofe 30, D-42279 Wuppertal, Germany

NAME AND LOCATION OF THE FACTORY

Schmersal Industrial Switchgear (Shanghai) Co.,Ltd.
No.3336 Caoying Road, Qingpu, Shanghai, P.R.China

PRODUCT NAME,MODEL AND SPECIFICATION

Safety Interlock Switch

AZM 150 Uimp: 4kV; Ui: 300V; Ith: 5A; AC-15: Ue/Ie:AC230V/4A; DC-13:
Ue/Ie:DC24V/4A; IP67, IP65 ; See the appendix

STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB/T 14048.5-2017

This is to certify that the above mentioned product(s) complies with the requirements of
implementation rules for compulsory certification(REFNO. CNCA-C03-02:2024).

Valid from: Jun.28,2024

Valid until: Jun.27,2029

The certificate information and validity could be checked by scanning the QR code below or logging in to
the website of the issuing authority, or on the website of the CNCA (www.cnca.gov.cn).



SIGNATURE:

谢肇煦



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.





CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

本翻译文件不具有法律效力，不得单独使用
This translated document does not have legal validity and cannot be used in isolation

CERTIFICATE NO. : 2024010305649334

Appendix : Page 1 of 2

3.3 型号的解释(Explanation of model/ type):		
	AZM150SK-(3a) R(5)(6)(7)-(8)-(9) AZM150(1)-(2)-(3b)R(4)(5)(6)-024-(8)-(9)	
	AZM150	基本开关名称
Nr.序号	Option 选项	Description 描述
	SK	Screw terminals 拧接
	R	Latching force 锁定力 50N
(1)	B	Actuator monitoring 操动件受监控
	Z	Guard locking function monitors 线圈, 受监控 (not in power to lock version) 仅使用与通电解锁版本)
(2)	ST	Connector plug M12 centre 带接线插头
	STR	Connector plug M12 right 右侧带内接线插座
	STL	Connector plug M12 left 左侧带内接线插座
		Magnet: 电磁铁: Actuator: 操动件:
(3a)	02 / 11	2 NC 2 常闭触点 1 NO/1 NC 1 常开, 1 常闭
	11 / 11	1 NO/1 NC 1 常开, 1 常闭 1 NO/1 NC 1 常开, 1 常闭
	11 / 02	1 NO/1 NC 1 常开, 1 常闭 2 NC 2 常闭触点
	02 / 02	2 NC 2 常闭触点 2 NC 2 常闭触点
	01 / 03	1 NC 1 常闭触点 3NC 3 常闭触点
	03 / 01	3 NC 3 常闭触点 1 NC 1 常闭触点
	01 / 12	1 NC 1 常闭触点 1NO 常开 2NC 2 常闭
(3b)	02 / 01	2 NC 2 常闭触点 1 NC 1 常闭触点
	02 / 10	2 NC 2 常闭触点 1 NO 1 常开
	10 / 02	1 NO 1 常开 2 NC 2 常闭触点
(4)	blank	Standard coding 标准编码
	I	Individually coding 特殊编码
(5)	blank	Power to unlock 通电开锁
	A	Power to lock 通电上锁
(6)	blank	Manual release 手动解锁
	T	Emergency exit 紧急出口
	N	Emergency release 紧急释放
(7)	024	Us 24 V DC
	110	Us 110 V AC
	230	Us 230 V AC

This page is attached to the certificate and should be used at the same time as the certificate page.



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.



CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

本翻译文件不具有法律效力，
不得单独使用
This translated document
does not have legal validity and
cannot be used in isolation

CERTIFICATE NO. : 2024010305649334

Appendix : Page 2 of 2

3.3 型号的解释(Explanation of model/ type): (续 continue)

Nr.序号	Option 选项	Description 描述
(8)	blank	No actuator included in delivery 产品不自带操动件, 需要客户单独购买
	B1	Incl. straight actuator B1 操动件B1
	B5	Incl. angled actuator B5 操动件B5
	B6L	Incl. flexible actuator B6, left 操动件B6, 左侧
	B6R	Incl. flexible actuator B6, right 操动件B6, 右侧
(9)	Blank	Standard 标准型
	0000-9999	表示客户特殊需求, 不影响开关基本结构和功能。

注: (2)~(9)可互换, 不影响开关基本结构和功能。
型号中出现的字母不区分大小写;
型号中出现的“空格”、“-”、“/”无任何技术含义, 仅增加可读性。



This page is attached to the certificate and should be used at the same time as the certificate page.



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.