



CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

本翻译文件不具有法律效力，
不得单独使用
This translated document
does not have legal validity and
cannot be used in isolation

CERTIFICATE NO.: 2024010305649335

NAME AND ADDRESS OF THE APPLICANT

Schmersal Industrial Switchgear (Shanghai) Co.,Ltd.
No.3336 Caoying Road, Qingpu, Shanghai, P.R.China

NAME AND ADDRESS OF THE MANUFACTURER

K.A. Schmersal GmbH & Co. KG
Moeddinghofe 30, D-42279 Wuppertal, Germany

NAME AND LOCATION OF THE FACTORY

Schmersal Industrial Switchgear (Shanghai) Co.,Ltd.
No.3336 Caoying Road, Qingpu, Shanghai, P.R.China

PRODUCT NAME,MODEL AND SPECIFICATION

Door Switch

AZ15,AZ16,AZ17,AZ335,AZ3350 Ui:500V(AZ15,AZ16,AZ17,AZ335),250V(AZ3350);
Uimp:6kV(AZ15,AZ16,AZ17,AZ335),4kV(AZ3350); Ith:10A; AZ15,AZ16,AZ335,AZ3350:AC-15: Ue/Ie:
AC230V/4A, DC-13: Ue/Ie: DC24V/4A; AZ17: AC-15: Ue/Ie: AC230V/4A; IP67 ; See the appendix

STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB/T 14048.5-2017

This is to certify that the above mentioned product(s) complies with the requirements of
implementation rules for compulsory certification(REFNO. CNCA-C03-02:2024).

Valid from: Jun.28,2024

Valid until: Jun.27,2029

The certificate information and validity could be checked by scanning the QR code below or logging in to
the website of the issuing authority, or on the website of the CNCA (www.cnca.gov.cn).



SIGNATURE:

谢肇煦



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.





CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

本翻译文件不具有法律效力，不得单独使用
This translated document does not have legal validity and cannot be used in isolation

CERTIFICATE NO. : 2024010305649335

Appendix : Page 1 of 3

Type description :

AZ 15: 4 处操动件插口, 仅 1 付触点。		
AZ 15Z(1)-(2)(3)		
(1)	VK	无特殊要求
	Vrk	扣紧力 30N
	O	使用-ZO 型开关盘及-ZO 型操动件
(2)	(空白) 或 M16	接线孔 M16
	M20	接线孔 M20
	ST	带内接线插座 M12*1
(3)	(空白)	标准型号, 无特殊需求
	-XXXX-XX	最多 3 组, X 由 0-9 数字标识, 代表客户特殊需求, 不影响开关基本结构和功能
注: (2)(3)的位置可互换, 不影响产品结构及性能 型号中出现的字母不区分大小写。 型号中出现的“-“ 或 ”/“无任何技术含义, 仅增加可读性。		
AZ 16: 4 处操动件插口, 可用 2-3 付触点		
AZ 16(1)ZV-(2)K(3)- (4)- (5) (6)		
(1)	(空白)	1 常开 1 常闭
	02	2 常闭
	03	3 常闭
	12	1 常开 2 常闭
(2)	(空白)	无特殊要求
	R	扣紧力 30N
(3)	G24	带 LED
(4)	(空白)	接线孔 M16
	M20	接线孔 M20
(5)	ST	底部带内接线插座 M12*1
	STL	左侧带内接线插座 M12*1
	STR	右侧带内接线插座 M12*1
(6)	(空白)	标准型号, 无特殊需求
	-XXXX-XX	最多 3 组, X 由 0-9 数字标识, 代表客户特殊需求, 不影响开关基本结构和功能。
注: (2)(3)的位置可互换, 不影响产品结构及性能 型号中出现的字母不区分大小写。 型号中出现的“-“ 或 ”/“无任何技术含义, 仅增加可读性。		

This page is attached to the certificate and should be used at the same time as the certificate page.



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.



CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

本翻译文件不具有法律效力，
不得单独使用
This translated document
does not have legal validity and
cannot be used in isolation

CERTIFICATE NO. : 2024010305649335

Appendix : Page 2 of 3

AZ 17: 2 处操作件插口, 有 2 付触点。

AZ 17Z(1)-Z(2)K-(3) (4)		
(1)	11	1 常开 1 常闭
	02	2 常闭
(2)	(空白)	扣紧力 5N
	R	扣紧力 30N
(3)	(空白)	接线孔 M16
	ST	带内接线插座 M12*1
(4)	(空白)	标准型号, 无特殊需求
	-XXXX-XX	最多 3 组, X 由 0-9 数字标识, 代表客户特殊需求, 不影响开关基本结构和功能
注: (3) (4) 的位置可互换, 不影响产品结构及性能 型号中出现的字母不区分大小写。 型号中出现的“-”或“/”无任何技术含义, 仅增加可读性。		

AZ 335: 4 处操作件插口, 可用 2-3 付触点, 铝合金外壳。

AZ 335- (1)-(2)(3)		
(1)	03zk	3 常闭
	03zrk	3 常闭
	12zk	1 常开 2 常闭
	12zrk	1 常开 2 常闭
(2)	(空白)	附件壳不转动
	U90	附件壳顺时针转动 90°
	U180	附件壳顺时针转动 180°
	U270	附件壳顺时针转动 270°
(3)	(空白)	标准型号, 无特殊需求
	-XXXX-XX	最多 3 组, X 由 0-9 数字标识, 代表客户特殊需求, 不影响开关基本结构和功能
注: (2)(3) 的位置可互换, 不影响产品结构及性能 型号中出现的字母不区分大小写。 型号中出现的“-”或“/”无任何技术含义, 仅增加可读性。		

This page is attached to the certificate and should be used at the same time as the certificate page.



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.



CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

本翻译文件不具有法律效力，
不得单独使用
This translated document
does not have legal validity and
cannot be used in isolation

CERTIFICATE NO. : 2024010305649335

Appendix : Page 3 of 3

AZ 3350: 1处操动件插口，可用2-3付触点，铝合金外壳。

AZ 3350- (1) -(2)(3)(4) (5) (6)		
(1)	03zk	3 常闭
	12zuek	1 常开 2 常闭
(2)	blank	银镍合金触点
	1637	镀金触点
(3)	blank	无特殊要求
	M16	接线孔 M16
	M20	接线孔 M20
(4)	blank	附件壳不转动
	U90	附件壳顺时针转动 90°
	U180	附件壳顺时针转动 180°
	U270	附件壳顺时针转动 270°
(5)	(空白)	不带带内接线插座
	ST	带内接线插座
	STD	带调节接线插座
(6)	(空白)	标准型号，无特殊需求
	-XXXX-XX	最多 3 组，X 由 0-9 数字标识，代表客户特殊需求，不影响开关基本结构和功能

注：(2)(3)(4)(5)的位置可互换，不影响产品结构及性能
型号中出现的字母不区分大小写。
型号中出现的“-“ 或 ”/“无任何技术含义，仅增加可读性。

This page is attached to the certificate and should be used at the same time as the certificate page.



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.