

Group: Switches

Type 1	PS 116 PS 2xx PS 3xx	235_236_255_256_EX 335_336_355_EX	BS65x_EX
Type 2	AZ 15 AZ 16_17_FB_EX	AZ 200 (A) AZ 201 AZ 300 (A)	AZ 415 AZ 3350_EX SCG_SDG_SHG TZG
for hinged guards	235_236 hinged switch 335_355_EX hinged switch	T.V10S 500 hinged switch TESF_TESZ hinged switch	TESK hinged switch
Enabling switches	ZSD 5_6		

Group: Sensors

BNS / Type 4 (3)	BNS 16 BNS 33_EX BNS 36 BNS 40S_EX	BNS 120_EX (3) BNS 180_EX (3) BNS 250_EX BNS 260	BNS 303_EX BNS-B20
Special / Type 4	BNS 30_300_333		
CSS / Type 4	CSS 16 (A) CSS 30 CSS 300	CSS 30S CSS 34 CSP 34 (A)	CSS 7-180 (A) CSS 8-180_EX
RSS / Type 4	RSS 16_EX RSS 36	RSS 260_Fx	

Group: Interlocks

Type 2	AZM 150 AZM 161_FB_EX	AZM 170_FB_EX AZM 190_TZK	AZM 415_EX TKM/F_TZM/F
Type 4	MZM 100 MZM 120 (A) AZM 200 (A) AZM 200 D (A)	AZM 201 AZM 201 SD AZM 201 D	AZM 300_EX AZM 300 SD AZM 40 AZM 400

Notice:

Interlocking function = Verriegelungsfunktion
Guard locking function = Zuhaltfunktion

Group: Optoelectronic devices

SLB	SLB 240	SLB 440	SLB 200 (A)	SLB 400 (A)
SLC	SLC 220 (A) SLC 420 (A) SLC 421 (A)	SLC 425I (A) SLC 440_Hx_EX SLC 440 COM	SLC 445 SLC 240 COM	
SLG	SLG 220 (A) SLG 420 SLG 422P (A)	SLG 425I (A) SLG 440_Hx_EX SLG 440 COM	SLG 445 SLG 240 COM	

(A) = Archive
"AZM300_EX"

Do not use this product for new projects !
Means "valid for" AZM300 AND AZM 300 EX !

Group: Tactile safety devices

Safety edges	SE-100 C	SE-304 C	SE-400 C
Safety mats	SMS 4_5		
Bumpers & cushion	SSG-SBL	SSG-SK	

Group: E-STOP devices

E-STOP	BDF 100	BDF 200 BDF 200-SD_FB	E-STOP general
Pull-wire switches	T3Z 068_EX	ZQ 700 ZQ 900_901_EX	RS65x_EX ZQ 215_315
Foot switches	TFH 232	T2FH 232	

Group: Two-Hand control panels

Two-Hand push buttons	SEPK02 SEPG05	SEP09	
------------------------------	------------------	-------	--

Group: Key trapped systems

Interlock		SHGV_EX	
Key-operated selector switch		SHGV/ESS_SVE_EX	

Group: Safety relays

STOP 0	SRB 20x (A) SRB 30x (A) SRB 400 (A)	SRB 504 (A) SRB K40	SRB-E-201ST_LC SRB-E-301ST SRB-E-402ST_OEMxx SRB-E-301MC SRB-E-302ST
Kat 1 / PL c	AES 1102, AES 1112		
Kat 3 / PL d	AES 113x, AES 116x, AES 1185, AES 12xx, AES 2xxx, AES 3075, AES 7112 (A)		
Kat 4 / PL e	AES 1337 (A)		
STOP 0 & STOP 1	SRB 211 (A) SRB 32x (A)		SRB-E-212ST_322ST SRB-E-232ST
STOP 1 & Special	SRB 031 SRB 100DR	SRB303SQP-SS	
Output expander	SRB 402 EM	SRB-E-402EM	SRB-E-602EM
Input expander	Protect-IE (A)	Protect-PE (A)	SRB-E-204ST_PE_OEMxx
FWS / TS / AZR	FWS 1205_1206 (A)	AZR 31S1	SRB-E-302FWS-TS_OEMxx
Standstill monitor & Time relay	FWS 2105_2505 (A)	SSW 301HV (A) SSW 303HV	SRB-E-402FWS-TS
SRB EXi	SRB 101EXi	SRB 200EXi	

(A) = Archive
"AZM300_EX"

Do not use this product for new projects !
Means "valid for" AZM300 AND AZM 300 EX !

Group: Safety Field Box

PROFINET	SFB-PN-IRT-8M12-IOP (A)
-----------------	-------------------------

PROFINET	SFB-PN-IRT-8M12-IOP-V2
-----------------	------------------------

EtherNet/IP	SFB-EIP-8M12-IOP
--------------------	------------------

EtherCAT	SFB-EC-8M12-IOP
-----------------	-----------------

(A) = Archive
"AZM300_EX"

Do not use this product for new projects !
Means "valid for" AZM300 **AND** AZM 300 EX !