



Content

1 About this document 1.1 Function
1.2 Target group: authorised qualified personnel. 1 1.3 Explanation of the symbols used. 1
1.4 Appropriate use
1.5 General safety instructions 1 1.6 Warning about misuse 2
1.7 Exclusion of liability .2
2 Product description
2.1 Ordering code
2.2 Special versions
2.3 Purpose
2.5 Safety classification
3 Mounting
3.1 General mounting instructions
3.2 Dimensions
4 Electrical connection
4.1 General information for electrical connection
5 Operating principle and settings
5.1 LED functions. .4 5.2 Description of the terminals. .4
5.3 Notes
6 Set-up and maintenance 6.1 Functional testing4
6.2 Maintenance
7 Discount have different
7 Disassembly and disposal 7.1 Disassembly
7.2 Disposal 4

SRB031MC

8	Appendix
---	----------

8.1 Wiring examples	5
8.2 Start configuration	5
8.3 Sensor configuration	5
8.4 Actuator configuration	6

EU Declaration of conformity

I. About this document

1.1 Function

This operating instructions manual provides all the information you need for the mounting, set-up and commissioning to ensure the safe operation and disassembly of the safety-monitoring module. The operating instructions must be available in a legible condition and a complete version in the vicinity of the device.

1.2 Target group: authorised qualified personnel

All operations described in this operating instructions manual must be carried out by trained specialist personnel, authorised by the plant operator only.

Please make sure that you have read and understood these operating instructions and that you know all applicable legislations regarding occupational safety and accident prevention prior to installation and putting the component into operation.

The machine builder must carefully select the harmonised standards to be complied with as well as other technical specifications for the selection, mounting and integration of the components.

1.3 Explanation of the symbols used

i

Information, hint, note: This symbol indicates useful additional information.

Caution: Failure to comply with this warning notice could lead to failures or malfunctions. **Warning:** Failure to comply with this warning notice could lead to physical injury and/or damage to the machine.

1.4 Appropriate use

The Schmersal range of products is not intended for private consumers.

The products described in these operating instructions are developed to execute safety-related functions as part of an entire plant or machine. It is the responsibility of the manufacturer of a machine or plant to ensure the correct functionality of the entire machine or plant.

The safety-monitoring module must be exclusively used in accordance with the versions listed below or for the applications authorised by the manufacturer. Detailed information regarding the range of applications can be found in the chapter "Product description".

1.5 General safety instructions

The user must observe the safety instructions in this operating instructions manual, the country specific installation standards as well as all prevailing safety regulations and accident prevention rules.

Further technical information can be found in the Schmersal catalogues or in the online catalogue on the Internet: products.schmersal.com.

The information contained in this operating instructions manual is provided without liability and is subject to technical modifications.

There are no residual risks, provided that the safety instructions as well as the instructions regarding mounting, commissioning, operation and maintenance are observed.

S SCHMERSAL

EN

1

1.6 Warning about misuse

In case of inadequate or improper use or manipulations of the safety-monitoring module, personal hazards or damage to machinery or plant components cannot be excluded. The relevant requirements of the standards EN ISO 14119 and EN ISO 13850 must be observed.

1.7 Exclusion of liability

We shall accept no liability for damages and malfunctions resulting from defective mounting or failure to comply with this operating instructions manual. The manufacturer shall accept no liability for damages resulting from the use of unauthorised spare parts or accessories.

For safety reasons, invasive work on the device as well as arbitrary repairs, conversions and modifications to the device are strictly forbidden, the manufacturer shall accept no liability for damages resulting from such invasive work, arbitrary repairs, conversions and/or modifications to the device.

The safety-monitoring module must only be used when the enclosure is closed, i.e. with the front cover fitted.

2. Product description

2.1 Ordering code

This operating instructions manual applies to the following types:

SRB031MC-24V

Drop-out delay preset in factory: 1.5 s / 1.1 s / 0.7 s / 0.4 s

> Only if the information described in this operating instructions manual are realised correctly, the safety function and therefore the compliance with the Machinery Directive is maintained.

2.2 Special versions

For special versions, which are not listed in the order code below 2.1, these specifications apply accordingly, provided that they correspond to the standard version.

2.3 Purpose

The safety-monitoring modules for integration in safety circuits are designed for fitting in control cabinets. They are used for the safe evaluation of the signals of positive break position switches or magnetic safety sensors for safety functions on sliding, hinged and removable safety guards as well as emergency stop control devices and AOPD's.

The safety function is defined as the delayed opening of the enabling circuits 17-18, 27-28 and 37-38 when the inputs S11-S12 and/or S21-S22 are opened. The safety-relevant current paths with the outputs contacts 17-18, 27-28 and 37-38 meet the following requirements under observation of a PFH value assessment (also refer to chapter 2.5 "Safety classification"):

- · Control category 3 PL e to EN ISO 13849-1
- SIL 3 to IEC 61508
- SIL CL 3 to EN 62061

To determine the Performance Level (PL) to EN ISO 13849-1 of the entire safety function (e.g. sensor, logic, actuator), an assessment of all relevant components is required.

> The entire concept of the control system, in which the safety component is integrated, must be validated to the relevant standards.

2.4 Technical data

General data:	
Standards:	EN 50178, EN ISO 13849-1
Climate resistance:	EN 60068-2-78
Mounting:	snaps onto standard rail to EN 60715
Terminal designations:	EN 60947-1
Material of the housings:	Plastic, glass-fibre reinforced thermoplastic,
	ventilated
Material of the contacts:	AgSnO, self-cleaning, positive drive
Weight:	250 g
Start conditions:	Automatic or start button
Feedback circuit (Y/N):	yes
Pull-in delay for automatic	start: typ. 100 ms
Pull-in delay with reset but	ton: typ. 20 ms
Drop-out delay in case of e	emergency stop: Delay time ±30% at 24 VDC
	and duty cycle (on-time) > 3.5 s
Drop-out delay in case of p	ower failure: Delay time ±30% at 24 VDC
	and duty cycle > 3.5 s
Drop-out delay in case of v	voltage drops: Delay time ±30% at 24 VDC
	and duty cycle (on-time) > 3.5 s
Bridging in case of voltage	drops: Delay time ±30% at 24 VDC and duty
	cycle (on-time) > 3.5 s
Mechanical data:	

Mechanical uala.	
Connection type:	Screw connection
Cable section:	0.25 2.5 mm ²
Connecting cable:	rigid or flexible
Tightening torque for the terminals:	0.6 Nm
With removable terminals (Y/N):	No
Mechanical life:	10 million operations
Electrical life:	Derating curve available on request
Resistance to shock:	30 g / 11 ms
Resistance to vibrations to EN 6006	68-2-6: 10 55 Hz,
	amplitude 0.35 mm
Ambient conditions:	

Amplent conditions:	
Ambient temperature:	−25 °C … +60 °C
Storage and transport temperature:	−40 °C … +85 °C
Degree of protection:	Enclosure: IP40
	Terminals: IP20

Insulation values to EN 60664-1

(Basic insulation between control cir	cuit and output circuit):
Rated insulation voltage U _i :	
- safety contact:	250 V
Rated impulse withstand voltage U _{imp} :	
- Safety contacts 17-18, 27-28 and 37-3	38: 4 kV
Overvoltage category:	III
Degree of pollution:	2
EMC rating:	to EMC Directive
Altitude:	max. 2,000 m
Electrical data:	
Contact resistance in new state:	max. 100 mΩ
Power consumption:	max. 2.0 W / 4.9 VA
Rated operating voltage U _e :	24 VDC -15% / +20%,
	residual ripple max. 10%,
	24 VAC -15% / +10%
Frequency range:	50 / 60 Hz
Fuse rating for the operating voltage:	Internal electronic trip, tripping
current > 50	00 mA, reset after approx. 1 sec.
Monitored inputs:	
Cross-wire detection (Y/N):	Yes
Wire breakage detection (Y/N):	Yes
Earth leakage detection (Y/N):	Yes
Number of NO contacts:	0
Number of NC contacts:	2
Cable length:	1,500 m mit 1.5 mm²
	2,500 m mit 2.5 mm ²
Conduction resistance:	max. 40 Ω

Clearance: IP54

Operating instructions Safety relay module

Outputs:	
Number of safety contacts:	3
Number of auxiliary contacts:	3 1 0
Number of signalling outputs:	0
Switching capacity of the safety contacts:	
- 17-18, 27-28, 37-38:	max. 250 V, 8 A ohmic
(inductive in case of appr	opriate protective wiring),
	min. 10 V / 10 mA,
Residual current at ar	mbient temperature up to:
45 °C: 24 A /	55 °C: 18 A / 60 °C: 12 A
Switching capacity of the auxiliary contacts:	45-46: 24 VDC / 2 A
Fuse rating of the safety contacts:	external (I _k = 1000 A)
	to EN 60947-5-1
Safety fuse 10 A	quick blow, 8 A slow blow
Fuse rating for the auxiliary contacts:	external (I _k = 1000 A)
	to EN 60947-5-1
Safety fuse 2.5 A	quick blow, 2 A slow blow
Utilisation category to EN 60947-5-1:	AC-15: 230 VAC / 6 A
	DC-13: 24 VDC / 6 A
The data specified in this manual is applicable	
operated with rated operating voltage $U_e \pm 0\%$	
ເຫຼັງ Use copper conductors only.	
Use 60°C/75°C conductors.	
Use No. 28-12 AWG wire size only.	
Tightening torque: 5 lb in.	
Use 60/75°C wire only.	

2.5 Safety classification

Standards:	EN ISO 13849-1, IEC 61508
PL:	up to e
Control category:	up to 3
PFH value:	≤ 2.00 × 10 ⁻⁷ /h
SIL:	up to 3
Mission time:	20 years

The PFH value of 2.00 × 10⁻⁷/h applies to the combinations of contact load (current through enabling contacts) and number of switching cycles (n_{op}/y) mentioned in the table below.

At 365 operating days per year and a 24-hours operation, this results in the below-mentioned switching cycle times (t_{cycle}) for the relay contacts. Diverging applications upon request.

Contact load	n _{op/y}	t _{cycle}
20 %	525,600	1.0 min
40 %	210,240	2.5 min
60 %	75,087	7.0 min
80 %	30,918	17.0 min
100 %	12,223	43.0 min

3. Mounting

3.1 General mounting instructions

Mounting: snaps onto standard rails to EN 60715. Snap the bottom of the enclosure slightly tilted forwards in the standard rail and push up until it latches in position.

To avoid EMC disturbances, the physical ambient and operational conditions at the place where the product is installed, must meet the provisions laid down in the paragraph "Electromagnetic Compatibility (EMC)" of EN 60204-1.

3.2 Dimensions

i

Device dimensions (H × W × D): 100 × 22.5 × 121 mm

4. Electrical connection

4.1 General information for electrical connection

As far as the electrical safety is concerned, the protection against unintentional contact of the connected and therefore electrically interconnected apparatus and the insulation of the feed cables must be designed for the highest voltage, which can occur in the device.



The electrical connection may only be carried out by authorised personnel in a de-energised condition.

Settle length x of the conductor: 8 mm



Wiring examples: see appendix

Operating instructions Safety relay module

SRB031MC

5. Operating principle and settings

5.1 LED functions

- K1: Status channel 1
- K2: Status channel 2
- U_B: Status operating voltage (LED is on, when the operating voltage on the terminals A1 - A2 is ON)
- Ui: Status internal operating voltage (LED is on, when the operating voltage on the terminals A1-A2 is ON and the fuse has not been triggered).

5.2 Description of the terminals

Voltages:	A1	+24 VDC/24 VAC
	A2	0 VDC/24 VAC
Inputs:	S11 - S12	Input channel 1 (+)
	S12 - S22	Input channel 2 (+)
	S21 - S22	Input channel 2 (-) (with cross-wire short
		detection)
Outputs:	17 - 18	First safety enabling circuit STOP 1
	27 - 28	Second safety enabling circuit (STOP 1)
	37 - 38	Third safety enabling circuit (STOP 1)
	45 - 46	Auxiliary NC contact as signalling contact
Start:	X1 - X2	Feedback circuit and external reset

5.3 Notes

<u>/</u>]	Signalling outputs must not be used in safety circuits.

Due to the operating principle of the electronic fuse, the customer must check that no hazard is caused by an unexpected restart in circuits without reset button (automatic reset).

- The safety enabling circuits 17 18 and 27 28 and 37 38 meet STOP category 1 to EN 60204-1.
- The drop-out delays of the safety enabling circuits can be reduced in case of a failure.

Opening the front cover (see Fig. 2)

- To open the front cover, insert a slotted screwdriver in the top and bottom cover notch and gently lift it.
- · When the front cover is open, the electrostatic discharge requirements must be respected and observed.
- After setting, the front cover must be fitted back in position.


Only touch the components after electrical discharge!

Setting the switch (see Fig. 3)

- · The cross-wire short monitoring function (factory setting) is programmed by means of the switch underneath the front cover of the safety-monitoring module.
- · The switch must only be operated in de-energised condition by means of a finger or an insulated blunt tool.
- · Pos. nQS (top): Not cross-wire short proof,
- suitable for 1-channel applications with outputs connected to potential in the control circuits.

Pos. QS (bottom), Cross-wire short proof:

suitable for 2-channel applications without outputs connected to potential in the control circuit s.



6. Set-up and maintenance

6.1 Functional testing

- The safety function of the safety-monitoring module must be tested. The following conditions must be previously checked and met:
- 1. Correct fixing.
- 2. Check the integrity of the cable entry and connections.
- 3. Check the safety-monitoring module's enclosure for damage.
- 4. Check the electrical function of the connected sensors and their influence on the safety-monitoring module and the downstream actuators

6.2 Maintenance

A regular visual inspection and functional test, including the following steps, is recommended:

- 1. Check the correct fixing of the safety-monitoring module.
- 2. Check the cable for damages.
- 3. Check electrical function.



If a manual functional check is necessary to detect a possible accumulation of faults, then this must take place during the intervals noted as follows:

- at least every month for PL e with category 3 or category 4 (according to EN ISO 13849-1) or SIL 3 with HFT (hardware fault tolerance) = 1 (according to EN 62061),
- at least every 12 months for PL d with category 3 (according to EN ISO 13849-1) or SIL 2 with HFT (hardware fault tolerance) = 1 (according to EN 62061)

Damaged or defective components must be replaced.

7. Disassembly and disposal

7.1 Disassembly

The safety-monitoring module must be disassembled in a de-energised condition only.

Push up the bottom of the enclosure and hang out slightly tilted forwards.

7.2 Disposal


The safety-monitoring module must be disposed of in an appropriate manner in accordance with the national prescriptions and legislations.

8. Appendix

8.1 Wiring examples

Dual-channel control, shown for a guard door monitor with two position switches where one has a positive break contact; with external reset button (\mathbb{R}) (see Fig. 4)

- Relay outputs: Suitable for 2-channel control, for increase in capacity or number of contacts by means of contactors or relays with positiveguided contacts.
- The control system recognises wire-breakage, earth faults and cross-wire shorts in the monitoring circuit.
- (H2) = Feedback circuit





8.2 Start configuration

External reset button (see Fig. 5)


The external reset button is integrated in the feedback circuit in series.
The manual start or the activation of the module occurs when the button is pressed (not when it is released!).

Automatic start (see Fig. 6)

- The automatic start is programmed by connecting the feedback circuit to the terminals X1 - X2. If the feedback circuit is not required, establish a bridge.
- Caution: Not admitted without additional measure due to the risk of gaining access by stepping behind!
- When the SRB301MC safety relay module is used with the operating mode "Automatic start", an automatic restart after a shutdown in case of emergency must be prevented by the upstream control to EN 60204-1 paragraph 9.2.3.4.2.



Due to the operating principle of the electronic fuse, the user must check that no hazard is caused by an unexpected restart in circuits without reset button (automatic reset).



8.3 Sensor configuration

Single-channel emergency stop circuit with command devices to EN ISO 13850 and EN 60947-5-5 (see Fig. 7)


- Wire breakage and earth leakage in the control circuits are detected.
- Category 1 PL c to EN ISO 13849-1 possible.

Dual-channel emergency stop circuit with command devices to EN ISO 13850 and EN 60947-5-5 (see Fig. 8)

- Wire breakage and earth leakage in the control circuits are detected.
- · Cross-wire shorts between the control circuits are not detected.
- Control category 3 PL e to EN ISO 13849-1 possible (with protective wiring)

Dual-channel emergency stop circuit with command devices to EN ISO 13850 and EN 60947-5-5 (see Fig. 9)

- Wire breakage and earth leakage in the control circuits are detected.
- · Cross-wire shorts between the control circuits are detected.
- Category 3 PL e to EN ISO 13849-1 possible.



Single-channel guard door monitoring circuit with interlocking devices to EN ISO 14119 (see Fig. 10)


- At least one contact with positive break required.
- Wire breakage and earth leakage in the control circuits are detected.
- Category 1 PL c to EN ISO 13849-1 possible.

Dual-channel guard door monitoring circuit with interlocking device to EN ISO 14119 (see Fig. 11)

- · At least one contact with positive break required.
- Wire breakage and earth leakage in the control circuits are detected.
- · Cross-wire shorts between the monitoring circuits are not detected.
- Control category 3 PL e to EN ISO 13849-1 possible (with protective wiring)

Dual-channel guard door monitoring circuit with interlocking device to EN ISO 14119 (Fig. 12)

- At least one contact with positive break required.
- Wire breakage and earth leakage in the control circuits are detected.
- Cross-wire shorts between the guard monitoring circuits are detected.
- Category 3 PL e to EN ISO 13849-1 possible.



Dual-channel control of a safety-related electronic (microprocessor-based) guard system with p-type transistor outputs (e.g. AOPDs) to EN IEC 61496 (see Fig. 13)

- Wire breakage and earth leakage in the control circuits are detected.
- The safety-monitoring module is not equipped with a cross-wire short detection here. The safety-relay module is not, therefore, equipped with a cross-wire short detection.
- If cross-wire shorts in the control circuits are detected by the safety guard: Control category 3 – PL e to EN ISO 13849-1 possible.

Dual-channel control of magnetic safety switches according to EN 60947-5-3 (see Fig. 14)

- Wire breakage and earth leakage in the control circuits are detected.
- · Cross-wire shorts between the control circuits are not detected.
- Control category 3 PL e to EN ISO 13849-1 possible (with protective wiring)

Dual-channel control of magnetic safety switches according to EN 60947-5-3 (see Fig. 15)

- Wire breakage and earth leakage in the control circuits are detected.
- · Cross-wire shorts between the control circuits are detected.
- Category 3 PL e to EN ISO 13849-1 possible.

The connection of magnetic safety switches to the SRB031MC safety-monitoring module is only admitted when

the requirements of the standard EN 60947-5-3 are observed. As the technical data are regarded, the following minimum

- requirements must be met:
- Switching capacity: min. 240 mW
- Switching voltage: min. 24 VDC
- switching current: min. 10 mA

For example, the following safety sensors meet the requirements:

- BNS 33-02Z-2187, BNS 33-02ZG-2187
- BNS 260-02Z, BNS 260-02ZG
- BNS 260-02-01Z, BNS 260-02-01ZG


When sensors with LED are wired in the control circuit (protective circuit), the following

- rated operating voltage must be observed and respected:
- 24 VDC with a max. tolerance of -5 %/+20 % • 24 VAC with a max. tolerance of -5 %/+10 %

S11 S21


T t

Otherwise availability problems could occur, especially in series-wired sensors, where a voltage drop in the control circuit is triggered by LEDs for instance.



i

nas as S12 S22 Fig. 14




8.4 Actuator configuration

Single-channel control (see Fig. 16)

- Suitable for increase in capacity or number of contacts by means of contactors or relays with positive-guided contacts.
- · If the feedback circuit
- is not required, establish a bridge.
- 🐵 = Feedback circuit

Dual-channel control with feedback circuit (see Fig. 17)

- · Suitable for increase in capacity or number of contacts by means of contactors or relays with positive-guided contacts.
- If the feedback circuit is not required, establish a bridge.
- 🐵 = Feedback circuit



9. EU Declaration of conformity

EU Declaration of con	formity	🕃 SCHMERSAI
Original	K.A. Schmersal GmbH & Co. KG Möddinghofe 30 42279 Wuppertal Germany Internet: www.schmersal.com	i
We hereby certify that the hereafter desc to the applicable European Directives.	ribed components both in their basic	design and construction conform
Name of the component:	SRB031MC	
Туре:	See ordering code	
Description of the component:	Safety relay module for emergency stop circuits, guard door monitoring, magnetic safety switches and AOPDs	
Relevant Directives:	Machinery Directive EMC-Directive RoHS-Directive	2006/42/EC 2014/30/EU 2011/65/EU
Applied standards:	EN 60947-5-1:2017 + AC:2020 EN ISO 13850:2015 EN ISO 13849-1:2015 EN ISO 13849-2:2012 EN 62061:2005 + AC:2010 + A1: EN 60664-1:2007 EN IEC 60664-1:2020 + AC:2020	
Notified body for the prototype test:	TÜV Rheinland Industrie Service GmbH Am Grauen Stein, 51105 Köln ID n°: 0035	
EC-prototype test certificate:	01/205/5035.02/22	
Person authorised for the compilation of the technical documentation:	Oliver Wacker Möddinghofe 30 42279 Wuppertal	
Place and date of issue:	Wuppertal, February 22, 2022	7
	Authorised signature Philip Schmersal Managing Director	

1

The currently valid declaration of conformity can be downloaded from the internet at products.schmersal.com.



K.A. Schmersal GmbH & Co. KG

Möddinghofe 30, 42279 Wuppertal Germany Phone: +49 202 6474-0 Telefax: +49 202 6474-100 E-Mail: info@schmersal.com Internet: www.schmersal.com