SCHMERSAL

EN

Operating instructions. pages 1 to 6 Original

Content

Appendix

8.1	Wiring examples			 								
8.2	Integral System Diagnostics (IS	SD)	 								

9 Declaration of conformity

1. About this document

1.1 Function

This operating instructions manual provides all the information you need for the mounting, set-up and commissioning for the safe operation and disassembly of the safety-monitoring module. the operating instructions must be available in a legible condition and a complete version in the vicinity of the device.

1.2 Target group: authorised qualified personnel

All operations described in this operating instructions manual must be carried out by trained specialist personnel, authorised by the plant operator only.

Please make sure that you have read and understood these operating instructions and that you know all applicable legislations regarding occupational safety and accident prevention prior to installation and putting the component into operation.

The machine builder must carefully select the harmonised standards to be complied with as well as other technical specifications for the selection, mounting and integration of the components.

1.3 Explanation of the symbols used



Information, hint, note:

This symbol is used for identifying useful additional information.



Caution: Failure to comply with this warning notice could lead to failures or malfunctions.

Warning: Failure to comply with this warning notice could lead to physical injury and/or damage to the machine.

1.4 Appropriate use

The Schmersal range of products is not intended for private consumers.

The products described in these operating instructions are developed to execute safety-related functions as part of an entire plant or machine. It is the responsibility of the manufacturer of a machine or plant to ensure the correct functionality of the entire machine or plant.

The safety-monitoring module must be exclusively used in accordance with the versions listed below or for the applications authorised by the manufacturer. Detailed information regarding the range of applications can be found in the chapter "Product description".

1.5 General safety instructions

The user must observe the safety instructions in this operating instructions manual, the country specific installation standards as well as all prevailing safety regulations and accident prevention rules.



Further technical information can be found in the Schmersal catalogues or in the online catalogue on the Internet: products.schmersal.com.

The information contained in this operating instructions manual is provided without liability and is subject to technical modifications.

There are no residual risks, provided that the safety instructions as well as the instructions regarding mounting, commissioning, operation and maintenance are observed.

Operating instructions Safety-monitoring module

1.6 Warning about misuse



In case of inadequate or improper use or manipulations of the safety-monitoring module, personal hazards or damages to machinery or plant components cannot be excluded.

1.7 Exclusion of liability

We shall accept no liability for damages and malfunctions resulting from defective mounting or failure to comply with this operating instructions manual. The manufacturer shall accept no liability for damages resulting from the use of unauthorised spare parts or accessories.

For safety reasons, invasive work on the device as well as arbitrary repairs, conversions and modifications to the device are strictly forbidden; the manufacturer shall accept no liability for damages resulting from such invasive work, arbitrary repairs, conversions and/or modifications to the device.

2. Product description

2.1 Ordering code

This operating instructions manual applies to the following types:

AES 113①

No.	Option	Description	
1	5	without start-up test with start-up test	

AES 114①

No.	Option	Description					
1	5	without start-up test with start-up test					



Only if the information described in this operating instructions manual are realised correctly, the safety function and therefore the compliance with the Machinery Directive is maintained.

2.2 Special versions

For special versions, which are not listed in the order code below 2.1, these specifications apply accordingly, provided that they correspond to the standard version.

2.3 Purpose

The safety-monitoring modules for integration in safety circuits are designed for fitting in control cabinets. They are used for the safe evaluation of the signals of positive break position switches for safety functions or magnetic safety sensors on sliding, hinged and removable safety guards as well as emergency stop control devices.

Design

The safety-monitoring modules have a dual-channel structure. They contain two safety relays with monitored positively driven contacts. The NO contacts of the relays, which are wired in series, build the enabling contacts.



The entire concept of the control system, in which the safety component is integrated, must be validated to the relevant standards.

2.4 Technical data

2.4 recillical uala	
Standards:	EN 60204-1, EN 60947-5-3,
0.00	EN ISO 13849-1, IEC 61508
Start conditions:	Automatic
Feedback circuit available:	no no
Start-up test:	AES5: no, AES6: yes
Pull-in delay for automatic start:	adjustable 0.1 / 1.0 s
Drop-out delay in case of "emergency stop	
Rated operating voltage U _e :	24 VDC
Rated operating current I _e :	0.2 A
Rated insulation voltage U _i :	250 V
Rated impulse withstand voltage U _{imp} :	4 kV
Thermal test current I _{the} :	6 A
Internal electronic fuse:	no
Power consumption:	< 5 W
Monitored inputs:	
Cross-wire short detection:	yes
Wire breakage detection:	yes
Earth connection detection:	yes
Number of NC contacts:	convertible 1NC → 2NC
Number of NO contacts:	convertible 1NO → 0NO
Outputs:	
Stop category 0:	1
Stop category 1:	0
Number of safety contacts:	1
Number of auxiliary contacts:	0
Number of signalling outputs:	2
Switching capacity of the safety contacts:	max. 6 A
Switching capacity of the signalling outputs	
Utilisation category to EN 60947-5-1:	AC-15: 230 V / 3 A
g,	DC-13: 24 V / 2 A
Max. fuse rating of the safety contacts:	6 A gG D-fuse
Fuse rating of the signalling outputs:	07.1902.1800
- AES 1135/1136:	short-circuit proof,
- AES 1145/1146:	short-circuit proof, p-type
Mechanical life:	20 million operations
LED display:	ISD
Ambient conditions:	100
Operating temperature:	0 °C +55 °C
Storage and transport temperature:	−25 °C +70 °C
	Enclosure: IP40
Degree of protection:	
	Terminals: IP20
D (Clearance: IP54
Degree of pollution:	2
	nto standard rail to EN 60715
Connection type:	Screw connection
Min. cable section:	0.25 mm ²
	ak aalid atrond ar multi atrond
	n², solid strand or multi-strand
lead	(including conductor ferrules)
lead Tightening torque:	(including conductor ferrules) 0.6 Nm
lead Tightening torque:	(including conductor ferrules)

2.5 Safety classification

Standards:	EN ISO 13849-1, IEC 61508
PL:	up to d
Category:	up to 3
SIL:	up to 2
B _{10D} (light load):	20,000,000 switching cycles
B _{10D} (nominal load):	400,000 switching cycles
Mission time:	20 years

$$\mbox{MTTF}_{\mbox{\scriptsize D}} = \frac{\mbox{B_{10D}}}{\mbox{\scriptsize 0,1 x n_{op}}} \qquad \mbox{n_{op}} = \frac{\mbox{d_{op} x h_{op} x $3600 s/h}}{\mbox{$t_{cycle}$}} \label{eq:nop}$$

 $\begin{array}{ll} n_{op} & = \text{average number of activations per year} \\ d_{op} & = \text{average number of operating days per year} \\ h_{op} & = \text{average number of operating hours per day} \\ t_{cycle} & = \text{average demand rate of the safety function in s} \\ & (e.g.~4 \times \text{per hour} = 1 \times \text{per } 15 \text{ min.} = 900 \text{ s}) \end{array}$

Operating instructions Safety-monitoring module

3. Mounting

3.1 General mounting instructions

Mounting: snaps onto standard rails to EN 60715.

3.2 Dimensions

Device dimensions (H/W/D): 100 x 22.5 x 121 mm

4. Electrical connection

4.1 General information for electrical connection



The electrical connection may only be carried out by authorised personnel in a de-energised condition.

Settle length x of the conductor: 8 mm



Wiring examples: see appendix



To avoid EMC disturbances, the physical ambient and operational conditions at the place where the product is installed, must meet the provisions laid down in the paragraph "Electromagnetic Compatibility (EMC)" of EN 60204-1.

5. Operating principle and settings

5.1 Operating principle after the operating voltage is switched on Without start-up test AES 1135 / AES 1145:

- 1. The functionality of the safety-monitoring module is tested.
- If the safety guard is closed or the emergency stop button released, the enabling paths of the safety-monitoring module will close. The LED is green.
- 3. The cable and the connected safety switch are only tested when the safety guard is opened or the emergency stop button when actuated

With start-up test AES 1136 / AES 1146:

- 1. The functionality of the safety-monitoring module is tested.
- The safety guard or the emergency stop button must be actuated, in order to check the cables and the connected safety switch (start-up test).
- If the safety guard is closed or the emergency stop button released, the enabling paths of the safety-monitoring module will close.
 The LED is green.

If the safety guard is opened or the emergency-stop button is actuated, the enabling paths of the safety-monitoring module will open. The machine is stopped and the LED flashes yellow.

Inputs: S14/S22

Connect a safety switch with one NC and one NO contact or two safety switches with one contact each or an emergency-stop button at input \$14/\$22

Safety switch with two NC contacts: X1

For an operation with two NC contacts, input X1 must be supplied with 24 VDC.

Outputs

Enabling paths 13-14: NO contacts for safety functions

Additional outputs Y1/Y2:

AES 1135/1136 Y1: Authorized operation (release output closed)

Y2: No authorized operation (release output

opened)

AES 1145/1146 Y1: Safety guard opened

(release output opened)

Y2: Failure (release output opened)

The additional outputs Y1 and Y2 must not be integrated in the safety circuit; they may only be used for signalling purposes.

Enable delay time

The enable delay time can be increased from 0.1 s to 1 s by changing the position of a jumper link connection. Remove the enclosure cover carefully by means of a screwdriver. Change the position of the jumper link connection B1.

Jumper link connection closed = 1 s

6. Set-up and maintenance

6.1 Functional testing

The safety function of the safety-monitoring module must be tested. The following conditions must be previously checked and met:

- 1. Correct fitting of the safety-monitoring module
- 2. Fitting and integrity of the power cable

6.2 Maintenance

In the case of correct installation and adequate use, the safety-monitoring module features maintenance-free functionality.

A regular visual inspection and functional test, including the following steps, is recommended:

- Check the correct fixing of the safety monitoring module
- Check the cable for damage.

Damaged or defective components must be replaced.

7. Disassembly and disposal

7.1 Disassembly

The safety monitoring module must be disassembled in the deenergised condition only.

7.2 Disposal

The safety monitoring module must be disposed of in an appropriate manner in accordance with the national prescriptions and legislations.




Operating instructions Safety-monitoring module


8. Appendix

8.1 Wiring examples

The application examples shown are suggestions. They however do not release the user from carefully checking whether the switchgear and its set-up are suitable for the individual application.

The wiring diagram is shown with guard doors closed and in a deenergised condition. Inductive loads (e.g. contactors, relays, etc.) are to be provided with suitable interference suppression circuitry. Do not connect additional loads to terminal S..





Key

→ Positive break

A [⊕ Non-contact safety sensor

A Safety switch

8.2 Integral System Diagnostics (ISD)

The LED indication of the safety-monitoring modules shows the different switching conditions and errors. The following tables show the different switching conditions.

Tables switching condition indication

Diagnostic LED	System condition
The LED is green.	Enabling paths closed
LED flashes yellow (0.5 Hz)	Enabling paths open
LED flashes yellow (2 Hz)	Safety guard closed, however no release; possible causes: incorrect operation (only one contact actuated upon opening) or voltage drop → perform start-up test

In case of error messages, the LED lights orange intermittently. During these intermissions, the LED flashes one up to seven times with short pulses.

Table error indications

Indication (orange) LED	Error	Cause
1 impulse	Inputs S1	Defective supply voltage lead, defective switch, erroneous fitting of the switch; switch only partially ac- tuated* for at least 5 s
4 impulses	Interference signals at the inputs (no safe evaluation assured)	Too high capacitive or inductive interference at the switch's cables or the supply voltage lead
5 impulses	One or both relays did not close within the monitoring time	Too low operating voltage U _e ; defective relay
6 impulses	Relay not disabled upon the actuation of the switch	May be due to contact welding
7 impulses	Dynamic monitoring of both channels (cross-monitoring) failure	Fault in one channel; internal data transmis- sion interrupted

^{*} Partial actuation: position of the switch, in which only one contact was actuated.

Deleting the error message

The fault message is deleted once the fault has been rectified and after the connected switch has been actuated to check the various functions.

9. Declaration of conformity

We declare under our sole responsibility that the products mentioned comply with all relevant provisions of the directives and regulations listed below and conform to the following standards.

Relevant Directives:

 ϵ

Machinery Directive EMC-Directive RoHS-Directive

2006/42/EC 2014/30/EU 2011/65/EU

Applied standards:

DIN EN 60947-5-1:2018 DIN EN ISO 13849-1:2016 DIN EN ISO 13849-2:2013



The currently valid declaration of conformity can be downloaded from the internet at products.schmersal.com.

K.A. Schmersal GmbH & Co. KG

Möddinghofe 30, 42279 Wuppertal Germany

Phone: +49 202 6474-0
Telefax: +49 202 6474-100
E-Mail: info@schmersal.com
Internet: www.schmersal.com