



Operating Instructionspages 1 to 6

Content

1 About this document 1.1 Function
1.2 Target group: authorised qualified personnel1 1.3 Explanation of the symbols used1
1.4 Appropriate use
1.5 General safety instructions1
1.6 Warning about misuse
1.7 Exclusion of liability2
2 Product description
2.1 Ordering code
2.2 Special versions2
2.3 Purpose
2.4 Technical data
2.5 Safety classification
3 Mounting
3.1 General mounting instructions
3.2 Dimensions
4 Electrical connection
4.1 General information for electrical connection.
5 Operating principle and settings
5.1 LED functions
5.2 Description of the terminals
5.3 Notes
6 Set-up and maintenance
6.1 Functional testing4
6.2 Maintenance
7 Disassembly and disposal
7 Disassembly and disposal 7.1 Disassembly
7 2 Disposal 4

SRB301ST 230V

8 Appendix

8.1 Wiring examples	4
8.2 Start configuration	4
8.3 Sensor configuration	5

8.4 Actuator configuration

9 EU Declaration of conformity

1. About this document

1.1 Function

This operating instructions manual provides all the information you need for the mounting, set-up and commissioning to ensure the safe operation and disassembly of the safety-monitoring module. The operating instructions must be available in a legible condition and a complete version in the vicinity of the device.

1.2 Target group: authorised qualified personnel

All operations described in this operating instructions manual must be carried out by trained specialist personnel, authorised by the plant operator only.

Please make sure that you have read and understood these operating instructions and that you know all applicable legislations regarding occupational safety and accident prevention prior to installation and putting the component into operation.

The machine builder must carefully select the harmonised standards to be complied with as well as other technical specifications for the selection, mounting and integration of the components.

1.3 Explanation of the symbols used

Information, hint, note: This symbol indicates useful additional information.

Caution: Failure to comply with this warning notice could lead to failures or malfunctions. **Warning:** Failure to comply with this warning notice could lead to physical injury and/or damage to the machine.

1.4 Appropriate use

i

The Schmersal range of products is not intended for private consumers.

The products described in these operating instructions are developed to execute safety-related functions as part of an entire plant or machine. It is the responsibility of the manufacturer of a machine or plant to ensure the correct functionality of the entire machine or plant.

The safety-monitoring module must be exclusively used in accordance with the versions listed below or for the applications authorised by the manufacturer. Detailed information regarding the range of applications can be found in the chapter "Product description".

1.5 General safety instructions

The user must observe the safety instructions in this operating instructions manual, the country specific installation standards as well as all prevailing safety regulations and accident prevention rules.

Further technical information can be found in the Schmersal catalogues or in the online catalogue on the Internet: products.schmersal.com.

The information contained in this operating instructions manual is provided without liability and is subject to technical modifications.

There are no residual risks, provided that the safety instructions as well as the instructions regarding mounting, commissioning, operation and maintenance are observed.



Ť

1.6 Warning about misuse



In case of inadequate or improper use or manipulations of the safety-monitoring module, personal hazards or damages to machinery or plant components cannot be excluded. The relevant requirements of the standards EN ISO 14119 and EN ISO 13850 must be observed.

1.7 Exclusion of liability

We shall accept no liability for damages and malfunctions resulting from defective mounting or failure to comply with this operating instructions manual. The manufacturer shall accept no liability for damages resulting from the use of unauthorised spare parts or accessories.

For safety reasons, invasive work on the device as well as arbitrary repairs, conversions and modifications to the device are strictly forbidden; the manufacturer shall accept no liability for damages resulting from such invasive work, arbitrary repairs, conversions and/or modifications to the device.

The safety-monitoring module must only be used when the enclosure is closed, i.e. with the front cover fitted.

2. Product description

2.1 Ordering code

This operating instructions manual applies to the following types:

SRB301ST 230V

Only if the information described in this operating instructions manual are realised correctly, the safety function and therefore the compliance with the Machinery Directive is maintained.

2.2 Special versions

For special versions, which are not listed in the order code below 2.1, these specifications apply accordingly, provided that they correspond to the standard version.

2.3 Purpose

The safety-monitoring modules for integration in safety circuits are designed for fitting in control cabinets. They are used for the safe evaluation of the signals of positive break position switches for safety functions on sliding, hinged and removable safety guards as well as emergency stop control devices.

The safety function is defined as the opening of the enabling circuits 13-14, 23-24 and 33-34 when the inputs S11-S12 and/or S21-S22 are opened. The safety-relevant current paths with the outputs contacts 13-14, 23-24 and 33-34 meet the following requirements under observation of a PFH value assessment (also refer to chapter 2.5 "Safety classification"):

- Category 4 PL e to EN ISO 13849-1
- SIL 3 to EN 61508
- corresponds to SIL CL 3 to EN 62061

To determine the Performance Level (PL) to EN ISO 13849-1 of the entire safety function (e.g. sensor, logic, actuator), an assessment of all relevant components is required.

The entire concept of the control system, in which the safety component is integrated, must be validated to the relevant standards.

2.4. Technical data	
2.4 Technical data General data:	
	13850, EN ISO 13849-1, EN ISO 13849-2,
	EN 61508, EN 62061
Climate resistance:	EN 60068-2-78
Mounting:	snaps onto standard rail to EN 60715
Terminal designations:	EN 60947-1
Material of the housings: P	lastic, glass-fibre reinforced thermoplastic,
Material of the contacts:	ventilated AgSnO, self-cleaning, positive drive
Weight:	250 g
Start conditions:	Automatic or start button
Feedback circuit (Y/N):	Ves
Pull-in delay with reset button	
Pull-in delay for automatic sta	
Drop-out delay in case of eme	
Drop-out delay on "supply fail	
	240 VAC: typ. 300 ms
Bridging in case of voltage dro	
0 0 0	240 VAC: typ. 270 ms
Mechanical data:	
Connection type:	Screw connection
Cable section:	min. 0.25 mm ² / max. 2.5 mm ²
Connecting cable:	rigid or flexible
Tightening torque for the term	
With removable terminals (Y/N	
Mechanical life:	10 million operations
Electrical life:	Derating curve available on request
Resistance to shock:	10 g / 11 ms
Resistance to vibration in acc	, , , , , , , , , , , , , , , , , , , ,
A 11 / 11/1	amplitude 0.35 mm
Ambient conditions:	−25 °C +45 °C
Ambient temperature:	
Storage and transport temper	
Degree of protection:	Enclosure: IP40 Terminals: IP20
	Clearance: IP54
Insulation values to EN 606	
(Basic insulation between c	ontrol circuit and output circuit):
Rated insulation voltage Ui:	
- safety contact:	250 V
Rated impulse withstand volta	ige U _{imp} :
- safety contact 13-14, 23-24,	33-34: 4 kV
Overvoltage category:	III
Degree of pollution:	2
EMC rating:	to EMC Directive
Altitude:	max. 2,000 m
Electrical data:	
Contact resistance in new sta	
Power consumption:	max. 2.8 VA
Rated operating voltage U _e :	48 240 VAC
Frequency range:	50 / 60 Hz
Max. fuse rating of the operation	
- primary side F1:	safety fuse, tripping current > 0.5 A;
*	al electronic fuse, tripping current > 0.12 A
Current and voltage at:	
	S11-S12, S21-S22, X2-X3:
Manda and 1	
· ·	24 VDC, approx. 45 mA
Monitored inputs: Short-circuit recognition (Y/N)	24 VDC, approx. 45 mA
Short-circuit recognition (Y/N) Wire breakage detection (Y/N	24 VDC, approx. 45 mA : No): Yes
Short-circuit recognition (Y/N) Wire breakage detection (Y/N Earth leakage detection (Y/N)	24 VDC, approx. 45 mA No Ves Yes
Short-circuit recognition (Y/N) Wire breakage detection (Y/N Earth leakage detection (Y/N) Number of NO contacts:	24 VDC, approx. 45 mA No Yes Yes 0
Short-circuit recognition (Y/N) Wire breakage detection (Y/N Earth leakage detection (Y/N) Number of NO contacts: Number of NC contacts:	24 VDC, approx. 45 mA No Yes Yes 0 2
Short-circuit recognition (Y/N) Wire breakage detection (Y/N Earth leakage detection (Y/N) Number of NO contacts:	24 VDC, approx. 45 mA No Yes Yes 0 2 1,500 m with 1.5 mm ²
Short-circuit recognition (Y/N) Wire breakage detection (Y/N Earth leakage detection (Y/N) Number of NO contacts: Number of NC contacts:	24 VDC, approx. 45 mA No Yes Yes 0

Operating instructions Safety-monitoring module

|--|

Number of safety contacts:	3
Number of auxiliary contacts:	1
Number of signalling outputs:	0
Switching capacity of the safety contacts:	13-14; 23-24; 33-34:
max. 250 V, 6 A c	ohmic (inductive in case of
app	ropriate protective wiring);
	min. 10 V / 10 mA
Switching capacity of the auxiliary contacts:	41-42: 24 VAC/DC / 2 A
Fuse rating of the safety contacts:	external ($I_k = 1,000 \text{ A}$)
	to EN 60947-5-1
Safety fuse 8 A	quick blow, 6 A slow blow
Fuse rating for the auxiliary contacts:	external ($I_k = 1,000 \text{ A}$)
	to EN 60947-5-1
Safety fuse 2.5 A	quick blow, 2 A slow blow
Utilisation category to EN 60947-5-1:	AC-15: 230 VAC / 6 A
	DC-13: 24 VDC / 6 A
The data specified in this manual are applicab	le when the component is
operated with rated operating voltage $U_e \pm 0\%$.	

2.5 Safety classification

EN ISO 13849-1, EN 61508
up to e
up to 4
99% (high)
> 65 points
≤ 2.00 × 10 ⁻⁸ /h
up to 3
20 years

The PFH value of 2.00×10^{-8} /h applies to the combinations of contact load (current through enabling contacts) and number of switching cycles $(n_{\text{op/y}})$ mentioned in the table below. At 365 operating days per year and a 24-hours operation, this results in the below-mentioned switching cycle times (t_{cycle}) for the relay contacts. Diverging applications upon request.

Contact load	n _{op/y}	t _{cycle}
20 %	525,600	1.0 min
40 %	210,240	2.5 min
60 %	75,087	7.0 min
80 %	30,918	17.0 min
100 %	12,223	43.0 min

3. Mounting

3.1 General mounting instructions

Mounting: snaps onto standard rails to EN 60715.

Snap the bottom of the enclosure slightly tilted forwards in the DIN rail and push up until it latches in position.

To avoid EMC disturbances, the physical ambient and operational conditions at the place where the product is installed, must meet the provisions laid down in the paragraph "Electromagnetic Compatibility (EMC)" of EN 60204-1.

3.2 Dimensions

ĺ

Device dimensions (H/W/D): 100 x 22.5 x 121 mm with plugged-in terminals: 120 × 22.5 × 121 mm

4. Electrical connection

4.1 General information for electrical connection

The electrical connection may only be carried out by authorised personnel in a de-energised condition.

As far as the electrical safety is concerned, the protection against unintentional contact of the connected and therefore electrically interconnected apparatus and the insulation of the feed cables must be designed for the highest voltage, which can occur in the device.

Settle length x of the conductor: 7 mm



Wiring examples: see appendix

5. Operating principle and settings

5.1 LED functions

• K1: Status channel 1

- K2: Status channel 2
- Ui: Status internal operating voltage (LED is on, when the operating voltage on the terminals A1-A2 is ON and the fuse has not been triggered).

5.2 Description of the terminals

Voltages:	A1	48 240 VAC
	A2	48 240 VAC
Inputs:	S11-S12	Input channel 1 (+)
	S21-S22	Input channel 2 (+)
Outputs:	13-14	First safety enabling circuit
	23-24	Second safety enabling circuit
	33-34	Third safety enabling circuit
	41-42	Auxiliary NC contact as signalling contact
Start:	X2	Feedback circuit and external reset
	X3	Feedback circuit and automatic start



Fig. 1

Operating instructions Safety-monitoring module

5.3 Notes

Signalling outputs must not be used in safety circuits.

Due to the operating principle of the electronic fuse, the customer must check that no hazard is caused by an unexpected restart in circuits without reset button (automatic start).

6. Set-up and maintenance

6.1 Functional testing

The safety function of the safety-monitoring module must be tested. The following conditions must be previously checked and met:

- 1. Correct fixing
- 2. Check the integrity of the cable entry and connections
- 3. Check the safety-monitoring module's enclosure for damage.
- 4. Check the electrical function of the connected sensors and their influence on the safety-monitoring module and the downstream actuators

6.2 Maintenance

A regular visual inspection and functional test, including the following steps, is recommended:

- 1. Check the correct fixing of the safety-monitoring module
- 2. Check the cable for damages
- 3. Check electrical function

The device has to be integrated into the periodic check-ups according to the Ordinance on Industrial Safety and Health, however at least 1 × year.

Damaged or defective components must be replaced.

7. Disassembly and disposal

7.1 Disassembly

The safety-monitoring module must be disassembled in a de-energised condition only

Push up the bottom of the enclosure and hang out slightly tilted forwards

7.2 Disposal

The safety relay module must be disposed of in an appropriate manner in accordance with the national prescriptions and legislations.

8.1 Wiring examples

8. Appendix

Dual-channel control, shown for a guard door monitor with two position switches A and B where one has a positive break contact; with external reset button (R) (see Fig. 2)

- · Relay outputs: Suitable for 2-channel control, for increase in capacity or number of contacts by means of contactors or relays with positiveguided contacts.
- · The control system recognises wire-breakage in the monitoring circuit. • 🐵 = Feedback circuit




Fig. 2 a) Logic


8.2 Start configuration

External reset button (with edge detection) (see Fig. 3)

- · The external reset button is integrated as shown.
- The safety-relay module is activated by the reset (after release) of the reset button (= detection of the trailing edge). Faults in the reset button, e.g. welded contacts or manipulations which could lead to an inadvertent restart, are detected in this configuration and will result in an inhibition of the operation.

Automatic start (see Fig. 4)

- · The automatic start is programmed by connecting the feedback circuit to the terminals. If the feedback circuit is not required, establish a bridge.
- · Caution: Not admitted without additional measure due to the risk of gaining access by stepping behind!
- Caution: within the meaning of EN 60204-1, paragraph 9.2.3.4.2, the operating mode "automatic start" is only restrictedly admissible. In particular, any inadvertent restart of the machine must be prevented by other suitable measures.



Operating instructions Safety-monitoring module

8.3 Sensor configuration

Single-channel emergency stop circuit with command devices to EN ISO 13850 and EN 60947-5-5 (see Fig. 5)


- Wire breakage and earth leakage in the control circuits are detected.
- Category 1 PL c to EN ISO 13849-1 possible, when tested to EN ISO 13849-1

Dual-channel emergency stop circuit with command devices to EN ISO 13850 and EN 60947-5-5 (see Fig. 6)

- Wire breakage and earth leakage in the control circuits are detected.
- Cross-wire shorts between the control circuits are not detected.
- Control category 4 PL e to EN ISO 13 849-1 possible (with protective wiring)

Single-channel guard door monitoring circuit with interlocking devices to EN ISO 14119 (see Fig. 7)

- At least one contact with positive break required.
- Wire breakage and earth leakage in the control circuits are detected.
- Category 1 PL c to EN ISO 13849-1 possible, when tested to EN ISO 13849-1



Dual-channel guard door monitoring circuit with interlocking device to EN ISO 14119 (see Fig. 8)

- With at least one positive-break position switch
- Wire breakage and earth leakage in the control circuits are detected.
- Cross-wire shorts between the control circuits are not detected.
- Control category 4 PL e to EN ISO 13 849-1 possible (with protective wiring)




Fig. 8

8.4 Actuator configuration

Single-channel control with feedback circuit (see Fig. 9)

- Suitable for increase in capacity or number of contacts by means of contactors or relays with positive-guided contacts.
- = feedback circuit:
- If the feedback circuit is not required, establish a bridge.

Dual-channel control with feedback circuit (see Fig. 10)

- Suitable for increase in capacity or number of contacts by means of contactors or relays with positive-guided contacts.
- 🐵 = feedback circuit:
- If the feedback circuit is not required, establish a bridge.






Fig. 10



9. EU Declaration of conformity

EU Declaration of conf		
Original	K.A. Schmersal GmbH & Co. H Möddinghofe 30 42279 Wuppertal Germany Internet: www.schmersal.com	ΚG
We hereby certify that the hereafter descri to the applicable European Directives.	bed components both in their ba	sic design and construction conform
Name of the component:	SRB301ST 230V	
Description of the component:	Safety-monitoring module for e and guard door monitoring	emergency stop circuits
Relevant Directives:	Machinery Directive EMC-Directive RoHS-Directive	2006/42/EC 2014/30/EU 2011/65/EU
Applied standards:	EN ISO 13850:2015 EN ISO 13849-1:2015 EN ISO 13849-2:2012 EN 61508:2010 EN 62061:2005 + AC:2010 + A	A1:2013 + A2:2015
Notified body for the prototype test:	TÜV Rheinland Industrie Servi Am Grauen Stein, 51105 Köln ID n°: 0035	
EC-prototype test certificate:	01/205/5160.02/22	
Person authorised for the compilation of the technical documentation:	Oliver Wacker Möddinghofe 30 42279 Wuppertal	
Place and date of issue:	Wuppertal, March 21, 2022	2
	Anna	
	Authorised signature Philip Schmersal Managing Director	

1

The currently valid declaration of conformity can be downloaded from the internet at products.schmersal.com.

(EN)

X (6

K.A. Schmersal GmbH & Co. KG Möddinghofe 30, 42279 Wuppertal

Germany Phone: +49 202 6474-0 Telefax: +49 202 6474-100 E-Mail: info@schmersal.com Internet: www.schmersal.com