SCHMERSAL

EN	Operating instructions. Original		to 6
----	----------------------------------	--	------

C	o	ni	te	nt	

1.2 1.3 1.4 1.5 1.6	About this document Function 1 Target group: authorised qualified personnel 1 Explanation of the symbols used 1 Appropriate use 1 General safety instructions 1 Warning about misuse 2 Exclusion of liability 2
2.2 2.3 2.4	Product descriptionOrdering code2Special versions2Destination and use2Technical data2Safety classification3
	MountingGeneral mounting instructions3Dimensions3
4 4.1	Electrical connection General information for electrical connection
5.2	Operating principle and settings LED functions. 3 Description of the terminals 3 Circuit technical notes 3
	Set-up and maintenance Functional testing
	Disassembly and disposal Disassembly

8	Appendix	
•	, .ppoax	

8.1	Wiring examples	4
8.2	Start configuration	4
	Sensor configuration	
8 4	Actuator configuration	5

EU Declaration of conformity

1. About this document

1.1 Function

This operating instructions manual provides all the information you need for the mounting, set-up and commissioning to ensure the safe operation and disassembly of the safety-monitoring module. The operating instructions must be available in a legible condition and a complete version in the vicinity of the device.

1.2 Target group: authorised qualified personnel

All operations described in this operating instructions manual must be carried out by trained specialist personnel, authorised by the plant operator only.

Please make sure that you have read and understood these operating instructions and that you know all applicable legislations regarding occupational safety and accident prevention prior to installation and putting the component into operation.

The machine builder must carefully select the harmonised standards to be complied with as well as other technical specifications for the selection, mounting and integration of the components.

1.3 Explanation of the symbols used



Information, hint, note:

This symbol is used for identifying useful additional information.



Caution: Failure to comply with this warning notice could lead to failures or malfunctions.

Warning: Failure to comply with this warning notice could lead to physical injury and/or damage to the machine.

1.4 Appropriate use

Products in Schmersal's range are not intended to be used by private end consumers.

The products described in these operating instructions are developed to execute safety-related functions as part of an entire plant or machine. It is the responsibility of the manufacturer of a machine or plant to ensure the correct functionality of the entire machinery or plant.

The safety-monitoring module must be exclusively used in accordance with the versions listed below or for the applications authorised by the manufacturer. Detailed information regarding the range of applications can be found in the chapter "Product description".

1.5 General safety instructions

The user must observe the safety instructions in this operating instructions manual, the country-specific installation standards as well as all prevailing safety regulations and accident prevention rules.



Further technical information can be found in the Schmersal catalogues or in the online catalogue on the Internet: products.schmersal.com.

The information contained in this operating instructions manual is provided without liability and is subject to technical modifications.

There are no residual risks, provided that the safety instructions as well as the instructions regarding mounting, commissioning, operation and maintenance are observed.

1.6 Warning about misuse



In case of inadequate or improper use or manipulations of the safety-monitoring module, personal hazards or damage to machinery or plant components cannot be excluded. The relevant requirements of the standards EN ISO 14119 and EN ISO 13850 must be observed.

1.7 Exclusion of liability

We shall accept no liability for damages and malfunctions resulting from defective mounting or failure to comply with this operating instructions manual. The manufacturer shall accept no liability for damages resulting from the use of unauthorised spare parts or accessories.

For safety reasons, invasive work on the device as well as arbitrary repairs, conversions and modifications to the device are strictly forbidden; the manufacturer shall accept no liability for damages resulting from such invasive work, arbitrary repairs, conversions and/or modifications to the device.

The safety-monitoring module must only be used when the enclosure is closed, i.e. with the front cover fitted.

2. Product description

2.1 Ordering code

This operating instructions manual applies to the following types:

SRB301X1



Only if the information described in this operating instructions manual are realised correctly, the safety function and therefore the compliance with the Machinery Directive is maintained.

2.2 Special versions

For special versions, which are not listed in the order code below 2.1, these specifications apply accordingly, provided that they correspond to the standard version.

2.3 Destination and use

The safety-monitoring modules for integration in safety circuits are designed for fitting in control cabinets. They are used for the safe evaluation of the signals of positive break position switches for safety functions on sliding, hinged and removable safety guards as well as emergency stop control devices.

The safety function is defined as the opening of enabling circuits 13-14, 23-24 and 33-34 when the input U_B (L+)-A1 are opened. The safety-relevant current paths with the output contacts 13-14, 23-24 and 33-34 meet the following requirements under observation of a B_{100} value assessment (also refer to "Requirements to EN ISO 13849-1"):

- control category 4 PL e to EN ISO 13849-1
- corresponds to SIL 3 to IEC 61508
- corresponds to SIL CL 3 to EN 62061

To determine the Performance Level (PL) of the entire safety function (e.g. sensor, logic, actuator) to EN ISO 13849-1, an analysis of all relevant components is required.



The entire concept of the control system in which the safety component is integrated, must be validated to the relevant standards.

2.4 Technical data

2.4 Technical data	
General data:	
Standards:	EN 60204-1, EN 60947-5-1, EN ISO 13849-1, IEC 61508
Climate resistance:	EN 60068-2-78
Mounting:	Snaps onto standard rail to EN 60715
Terminal designations:	EN 60947-1
Material of the housings:	Plastic, glass-fibre reinforced
	thermoplastic, ventilated
Material of the contacts:	AgSnO, self-cleaning, positive drive
Weight:	220 g
Start conditions:	Automatic or start button
Feedback circuit (Y/N):	yes
Pull-in delay:	≤ 55 ms
Drop-out delay in case of "emerge	
Bridging in case of voltage drops:	
Mechanical data:	2 40 1113
Connection type:	Corour connection
	Screw connection
Cable section:	min. 0,25 mm² / max. 2,5 mm²
Connecting cable:	rigid or flexible
Tightening torque for the terminal	
With removable terminals (Y/N):	No
Mechanical life:	10 million operations
Electrical life:	Derating curve available on request
Resistance to shock:	10 g / 11 ms
Resistance to vibrations	
to EN 60068-2-6:	10 55 Hz, amplitude 0.35 mm
Ambient conditions:	·
Ambient temperature:	−25 °C +60 °C
Storage and transport temperatur	
Degree of protection:	Enclosure: IP40
9	Terminals: IP20
	Clearance: IP54
Air clearances and creepage	Glodianos. II o i
distances to EN 60664-1:	4 kV/2 (basic insulation)
EMC rating:	to EMC Directive
Electrical data:	to Livic Directive
	may 100 m
Contact resistance in new state:	max. 100 mΩ
Power consumption:	max. 1.4 W / 3.2 VA
Rated operating voltage U _e :	24 VDC –15% / +20%,
	residual ripple max. 10%,
	24 VAC -15% / +10%
Frequency range:	50 / 60 Hz
Fuse rating for the operating volta	
	tripping current > 1 A
Monitored inputs:	
Short-circuit recognition (Y/N):	No
Wire breakage detection (Y/N):	Yes
Earth leakage detection (Y/N):	Yes
Number of NO contacts:	0
Number of NC contacts:	
Cable length:	1,500 m mit 1.5 mm ²
9	2,500 m mit 2.5 mm ²
Conduction resistance:	max. 40 Ω
Outputs:	
Number of safety contacts:	3
Number of auxiliary contacts:	1
Number of signalling outputs:	0
Switching capacity of the safety of	
Switching capacity of the salety of	
	max. 250 V, 8 A ohmic (inductive in
	case of appropriate protective wiring);
0 11 11	min. 10 V / 10 mA
Switching capacity of the auxiliary	
Fuse rating of the safety contacts	
	to EN 60947-5-1
	ety fuse 10 A quick blow, 8 A slow blow
Fuse rating for the auxiliary conta	, ,
	to EN 60947-5-1
	ety fuse 2.5 A quick blow, 2 A slow blow
Utilisation category to EN 60947-	5-1: AC-15: 230 VAC / 6 A

DC-13: 24 VDC / 6 A

The data specified in this manual are applicable when the component is operated with rated operating voltage U_e ±0%.

2.5 Safety classification

Standards:	EN ISO 13849-1, IEC 61508
PL:	up to e
Control category:	up to 4
DC:	99% (high)
CCF:	> 65 points
PFH value:	≤ 2.00 × 10 ⁻⁸ /h
SIL:	up to 3
Mission time:	20 years

The PFH value of 2.00 × 10^{-8} /h applies to the combinations of contact load (current through enabling contacts) and number of switching cycles ($n_{op/y}$) mentioned in the table below. At 365 operating days per year and a 24-hours operation, this results in the below-mentioned switching cycle times (t_{cycle}) for the relay contacts.

Diverging applications upon request.

n _{op/y}	t _{cycle}
525,600	1.0 min
210,240	2.5 min
75,087	7.0 min
30,918	17.0 min
12,223	43.0 min
	525,600 210,240 75,087 30,918

3. Mounting

3.1 General mounting instructions

Mounting: snaps onto standard rails to EN 60715.

Snap the bottom of the enclosure slightly tilted forwards in the rail and push up until it latches in position.



To avoid EMC disturbances, the physical ambient and operational conditions at the place where the product is installed, must meet the provisions laid down in the paragraph "Electromagnetic Compatibility (EMC)" of EN 60204-1.

3.2 Dimensions

All measurements in mm.

Device dimensions (H/W/D): 100 x 22.5 x 121 mm

4. Electrical connection

4.1 General information for electrical connection



The electrical connection may only be carried out by authorised personnel in a de-energised condition.



As far as the electrical safety is concerned, the protection against unintentional contact of the connected and therefore electrically interconnected apparatus and the insulation of the feed cables must be designed for the highest voltage, which can occur in the device.

Settle length x of the conductor: 8 mm



Wiring examples: see appendix

5. Operating principle and settings

5.1 LED functions

- K1: Status channel 1
- K2: Status channel 2
- U_B: Status operating voltage (LED is on, when the operating voltage on the terminals A1-A2 is ON)
- U_i: Status internal operating voltage (LED is on, when the operating voltage on the terminals A1-A2 is ON and the fuse has not been triggered).

5.2 Description of the terminals

Voltages:	A1	+24 VDC/24 VAC
	A2	0 VDC/24 VAC
Outputs:	13-14	First safety enabling circuit
	23-24	Second safety enabling circuit
	33-34	Third safety enabling circuit
Start:	Y1-Y2	Feedback circuit and external reset
	41-42	Auxiliary NC contact as signalling contact



Fig. 1

5.3 Circuit technical notes



Signalling outputs must not be used in safety circuits.



Due to the operating principle of the electronic fuse, the customer must check that no hazard is caused by an unexpected restart in circuits without reset button (automatic reset).

6. Set-up and maintenance

6.1 Functional testing

The safety function of the safety-monitoring module must be tested. The following conditions must be previously checked and met:

- 1. Correct fixing
- 2. Check the integrity of the cable entry and connections
- 3. Check the safety-monitoring module's enclosure for damage.
- Check the electrical function of the connected sensors and their influence on the safety-monitoring module and the downstream actuators

6.2 Maintenance

A regular visual inspection and functional test, including the following steps, is recommended:

- 1. Check the correct fixing of the safety-monitoring module
- 2. Check the cable for damages
- 3. Check electrical function



If a manual functional check is necessary to detect a possible accumulation of faults, then this must take place during the intervals noted as follows:

- at least every month for PL e with category 3 or category 4 (according to EN ISO 13849-1) or SIL 3 with HFT (hardware fault tolerance) = 1 (according to EN 62061);
- at least every 12 months for PL d with category 3 (according to EN ISO 13489-1) or SIL 2 with HFT (hardware fault tolerance) = 1 (according to EN 62061).

Damaged or defective components must be replaced.

7. Disassembly and disposal

7.1 Disassembly

The safety-monitoring module must be disassembled in a de-energised condition only. Push up the bottom of the enclosure and hang out slightly tilted forwards.

7.2 Disposal

The safety-monitoring module must be disposed of in an appropriate manner in accordance with the national prescriptions and legislations.

8. Appendix

8.1 Wiring examples

One-channel control, shown for a guard door monitor with one positive break contact and external reset button (8) (see Fig. 2)

- Relay outputs: Suitable for 2-channel control, for increase in capacity or number of contacts by means of contactors or relays with positiveguided contacts.
- The control system recognises wire-breakage and earth faults in the monitoring circuit.
- (H2) = Feedback circuit




Fig. 2 a) Logic

8.2 Start configuration

External reset button (non-monitored start) (see Fig. 3)

- The external reset button is integrated in the feedback circuit in series.
- The safety-monitoring module is activated upon actuation of the reset button

Automatic start (see Fig. 4)

- The automatic start is programmed by connecting the feedback circuit to the terminals X1-X2. If the feedback circuit is not required, establish a bridge
- Caution: Not admitted without additional measure due to the risk of gaining access by stepping behind!
- When the SRB301X1 safety-monitoring module is used with the operating mode "Automatic start", an automatic restart after a shutdown in case of emergency must be prevented by the upstream control to EN 60204-1 paragraph 9.2.3.4.2.




8.3 Sensor configuration

Single-channel emergency stop circuit with command devices to EN ISO 13850 and EN 60947-5-5 (see Fig. 5)

- Wire breakage and earth le akage in the control circuits are detected.
- Possible control categories:
- Cat. 1 PL c to EN ISO 13849-1

Single-channel guard door monitoring circuit with interlocking devices to EN ISO 14119 (see Fig. 6)

- At least one contact with positive break required.
- Wire breakage and earth le akage in the control circuits are detected.
- · Possible control categories:
- Cat. 1 PL c to EN ISO 13849-1




8.4 Actuator configuration

Single-channel control (see Fig. 7)

- Suitable for increase in capacity or number of contacts by means of contactors or relays with positive-guided contacts.
- If the feedback circuit is not required, establish a bridge.
- H2 = Feedback circuit and external reset in series

Dual-channel control with feedback circuit (see Fig. 8)

- Suitable for increase in capacity or number of contacts by means of contactors or relays with positive-guided contacts.
- If the feedback circuit is not required, establish a bridge.
- (H2) = Feedback circuit and external reset in series



9. EU Declaration of conformity

EU Declaration of conformity

9 SCHMERSAL

K.A. Schmersal GmbH & Co. KG Original

Möddinghofe 30 42279 Wuppertal Germany

Internet: www.schmersal.com

We hereby certify that the hereafter described components both in their basic design and construction conform

to the applicable European Directives.

Name of the component: SRB301X1

Description of the component: Safety-monitoring module for emergency stop circuits and

guard door monitoring

Relevant Directives: Machinery Directive 2006/42/EC 2014/30/EU

EMC-Directive RoHS-Directive 2011/65/EU

Applied standards: EN 60947-5-1:2004 + AC:2005 + A1:2009

EN 60947-5-1:2017 EN ISO 13849-1:2015 EN ISO 13849-2:2012

Notified body, which approved TÜV Rheinland Industrie Service GmbH

the full quality assurance system, Am Grauen Stein, 51105 Köln

referred to in Appendix X, 2006/42/EC: ID n°: 0035

Person authorised for the compilation

Place and date of issue:

Oliver Wacker of the technical documentation: Möddinghofe 30 42279 Wuppertal

Authorised signature Philip Schmersal Managing Director

Wuppertal, November 22, 2021

Mund

SRB301X1-E-EN

The currently valid declaration of conformity can be downloaded from the internet at products.schmersal.com.





Möddinghofe 30, 42279 Wuppertal

Germany

Phone: +49 202 6474-0 Telefax: +49 202 6474-100 E-Mail: info@schmersal.com Internet: www.schmersal.com